

Choose Timken Strength

Timken® SAF Split-Block Housed Units offer rugged protection for spherical roller bearings



Find the size you need — fast.

- Standard shaft sizes ranging from 1-3/8 inch to 19-1/2 inch bore.
- Custom shaft sizes up to 40 inches.
- Metric bore sizes are available.

Reduce your downtime.

- Fast shipment on most standard shaft sizes.
- Comprehensive inventory levels of housings, bearings, mounting hardware and seals.

Choose the design you need.

- Tapered bore design for easy mounting.
- Straight bore design for better axial location.
- Readily convert the block from fixed to float by removing the stabilizing ring.

Order complete assembly or just a few parts.

- Well-stocked inventory typically enables quick shipment of standard parts and assemblies.

SAF Interchange Guide

Shaft Size	Timken PN	SKF	Dodge	Rexnord/LINK-BELT
1 7/16	SAF 22509	SAF 22509	P2B509-USAF-107LER	PLB6823R
1 15/16	SAF 22511	SAF 22511	P2B511-USAF-115LER	PLB6831R
2 7/16	SAF 22515	SAF 22515	P2B515-USAF-207LER	PLB6839R
2 7/16	FSAF 22515	FSAF 22515	P4B515-USAF-207LER	PLB6839FR
2 15/16	SAF 22517	SAF 22517	P2B517-USAF-215LER	PLB6847R
2 15/16	FSAF 22517	FSAF 22517	P4B517-USAF-215LER	PLB6847FR
2 15/16	SAF 22617	SAF 22617	P2B617-USAF-212LER	PLB6947R
3 7/16	SAF 22520	SAF 22520	P2B520-USAF-307LER	PLB6855R
3 7/16	FSAF 22520	FSAF 22520	P4B520-USAF-307LER	PLB6855FR
3 15/16	SAF 22522	SAF 22522	P4B522-USAF-315LER	PLB6863FR
3 15/16	SAF 22622	SAF 22622	P4B622-USAF-315LER	SAF22622315
4 7/16	SAF 22526	SAF 22526	P4B526-USAF-407LER	PLB6871FR
4 7/16	SAF 22626	SAF 22626	P4B626-USAF-407LER	SAF22626407
4 15/16	SAF 22528	SAF 22528	P4B528-USAF-415LER	PLB6879FR
5 7/16	SAF 22532	SAF 22532	P4B532-USAF-507LER	PLB6887FR
5 15/16	SAF 22534	SAF 22534	P4B534-USAF-515LER	PLB6883FR
6 7/16	SAF 22536	SAF 22536	P4B536-USAF-607LER	PLB68103FR
6 15/16	SAF 22538	SAF 22538	P4B538-USAF-615LER	PLB68111FR
7 15/16	SAF 22544	SAF 22544	P4B544-USAF-708LER	PLB68127FR
8 7/16	SAF 23048KX8 7/16	SAF 23048 KA x 8.7/16	P4B048-USAF-807LER	PLB66135FH
8 15/16	SAF 23048KX8 15/16	SAF 23048 KA x 8.15/16	P4B048-USAF-815LER	PLB23048K81516
9	SAF 048 X 9	SAF 23048 KA x 9	P4B048-USAF-900LER	PLB23048K9
9 7/16	SDAF 23152KX9 7/16	SDAF 23152 KA x 9.7/16	-	PLB23152K9716
9 7/16	SAF 23052KX9 7/16	SAF 23052 KA x 9.7/16	P4B052-USAF-907LER	PLB23052K9716
9 1/2	SDAF 23152KX 9 1/2	SDAF 23152 KA x 9.1/2	-	-
9 1/2	SAF 23052K X 9 1/2	SAF 23052 KA x 9.1/2	P4B052-USAF-908LER	PLB23052K912
9 15/16	SDAF23156KX9 15/16	SDAF 23156 KA x 9.15/16	-	-
9 15/16	SAF 23056KX9 15/16	SAF 23056 KA x 9.15/16	P4B056-USAF-915LER	PLB23056K91516
10	SAF 23056K X 10	SAF 23056 KA x 10	P4B056-USAF-1000LER	PLB23056K10
10	SDAF 23156K X 10	SDAF 23156 KA x 10	-	-
10 7/16	SAF 23056KX10 7/16	SAF 23056 KA x 10.7/16	P4B056-USAF-1007LER	PLB23056K10716
10 7/16	SDAF23156KX10 7/16	SDAF 23156 KA x 10.7/16	-	PLB23156K10716
10 1/2	SDAF 23156KX10 1/2	SDAF 23156 KA x 10.1/2	-	-
10 1/2	SAF 23056KX 10 1/2	SAF 23056 KA x 10.1/2	P4B056-USAF-1008LER	PLB66168FH
10 15/16	SDAF23060KX10 1516	SDAF 23060 KA x 10.15/16	-	PLB23060K101516
10 15/16	SDAF 23160K	SDAF 23160 KA x 10.15/16	-	PLB23160K101516
11 7/16	SDAF23064KX11 7/16	SDAF 23064 KA x 11.7/16	-	-
11 15/16	SDAF23064KX11 1516	SDAF 23064 KA x 11.15/16	-	PLB23064K111516
11 15/16	SDAF23164KX11 1516	SDAF 23164 KA x 11.15/16	-	PLB23164K111516
12 7/16	SDAF23168KX12 7/16	SDAF 23168 KA x 12.7/16	-	PLB23168K12716

Additional sizes available. Timken® is a registered trademark of The Timken Company. All other trademarks are the property of their respective owners.

TIMKEN

Choose Timken Strength

Timken® SAF Split-Block Housed Units offer rugged protection for spherical roller bearings

Timken® SAF Component Guide

Shaft Size	Timken PN	Bearing	Adaptor	Housing	Seals
1 7/16	SAF 22509	22209KCJW33C3	SNW-09 X 1 7/16	SAF 509	LER 17
1 15/16	SAF 22511	22211KEJW33C3	SNW-11 X 1 15/16	SAF 511	LER 24
2 7/16	SAF 22515	22215KCJW33C3	SNW-15 X 2 7/16	SAF 515	LER 37
2 7/16	FSAF 22515	22215KCJW33C3	SNW-15 X 2 7/16	FSAF 515	LER 37
2 15/16	SAF 22517	22217KCJW33C3	SNW-17 X 2 15/16	SAF 517	LER 53
2 15/16	FSAF 22517	22217KCJW33C3	SNW-17 X 2 15/16	FSAF 517	LER 53
2 15/16	SAF 22617	22317KCJW33C3	SNW-117 X 2 15/16	SAF 617	LER 53
3 7/16	SAF 22520	22220KEJW33C3	SNW-20 X 3 7/16	SAF 520	LER 102
3 7/16	FSAF 22520	22220KEJW33C3	SNW-20 X 3 7/16	FSAF 520	LER 102
3 15/16	SAF 22522	22222KEJW33C3	SNW-22 X 3 15/16	SAF 522	LER 109
3 15/16	SAF 22622	22322KCJW33C3	SNW-122 X 3 15/16	SAF 622	LER 109
4 7/16	SAF 22526	22226KCJW33C3	SNW-26 X 4 7/16	SAF 526	LER 117
4 7/16	SAF 22626	22326KCJW33C3	SNW-126 X 4 7/16	SAF 626	LER 117
4 15/16	SAF 22528	22228KCJW33C3	SNW-28 X 4 15/16	SAF 528	LER 122
5 7/16	SAF 22532	22232KCJW33C3	SNW-32 X 5 7/16	SAF 532	LER 130
5 15/16	SAF 22534	22234KCJW33C3	SNW-34 X 5 15/16	SAF 534	LER 140
6 7/16	SAF 22536	22236KCJW33C3	SNW-36 X 6 7/16	SAF 536	LER 148
6 15/16	SAF 22538	22238KEMB33C3	SNW-38 X 6 15/16	SAF 538	LER 155
7 15/16	SAF 22544	22244KYMBW507C08C3	SNW-44 X 7 15/16	SAF 544	LER 167
8 7/16	SAF 23048KX8 7/16	23048KYM33C08C3	SNP-3048 X 8 7/16	SAF 048 X 8 7/16	LER 526
8 15/16	SAF 23048KX8 15/16	23048KYM33C08C3	SNP-3048 X 8 15/16	SAF 048 X 8 15/16	LER 529
9	SAF 048 X 9	23048KYM33C08C3	SNP-3048 X 9	SAF 048K X 9	LER 530
9 7/16	SAF 23052KX9 7/16	23052KYMBW507C08C3	SNP-3052 X 9 7/16	SAF 052K X 9 7/16	LER 178-1
9 7/16	SDAF 23152KX9 7/16	23152KYMBW507C08C3	SNP-3152 X 9 7/16	SDAF 3152KX 9 7/16	ER 891
9 1/2	SAF 23052K X 9 1/2	23052KYMBW507C08C3	SNP-3052 X 9 1/2	SAF 052K X 9 1/2	LER 178
9 1/2	SDAF 23152KX 9 1/2	23152KYMBW507C08C3	SNP-3152 X 9 1/2	SDAF 3152K X 9 1/2	ER 842
9 15/16	SAF 23056KX9 15/16	23056KYMBW507C08C3	SNP-3056 X 9 15/16	SAF 056K X 9 15/16	ER 751
9 15/16	SDAF23156KX9 15/16	23156KYMBW507C08C3	SNP-3156 X 9 15/16	SDAF 3156KX9 15/16	ER 840
10	SAF 23056K X 10	23056KYMBW507C08C3	SNP-3056 X 10	SAF 056K X 10	ER 705
10	SDAF 23156K X 10	23156KYMBW507C08C3	SNP-3156 X 10	SDAF 3156K X 10	ER 845
10 7/16	SAF 23056KX10 7/16	23056KYMBW507C08C3	SNP-3056 X 10 7/16	SAF 056K X 10 7/16	ER 745
10 7/16	SDAF23156KX10 7/16	23156KYMBW507C08C3	SNP-3156 X 10 7/16	SDAF 3156K	ER 820
10 1/2	SAF 23056KX 10 1/2	23056KYMBW507C08C3	SNP-3056 X 10 1/2	SAF 056K X 10 1/2	ER 710
10 1/2	SDAF 23156KX10 1/2	23156KYMBW507C08C3	SNP-3156 X 10 1/2	SDAF 3156KX 10 1/2	ER 973
10 15/16	SDAF23060KX10 15/16	23060KYMBW507C08C3	SNP-3060X 10 15/16	SDAF 060KX10 15/16	ER 858
10 15/16	SDAF 23160K x 10 15/16	23160KYMBW507C08C3	SNP-3160X 10 15/16	SDAF3160KX10 15/16	ER 858
11 7/16	SDAF23064KX11 7/16	23064KYMBW507C08C3	SNP-3064 X 11 7/16	SDAF 064KX 11 7/16	ER 861
11 15/16	SDAF23064KX11 15/16	23064KYMBW507C08C3	SNP-3064X 11 15/16	SDAF 064KX11 15/16	ER 859
11 15/16	SDAF23164KX11 15/16	23164KYMBW507C08C3	SNP-3164X 11 15/16	SDAF 3164K	ER 900
12 7/16	SDAF23168KX12 7/16	23168KYMBW507C08C3	SNP-3168 X 12 7/16	SDAF 3168K	ER 975

* Housing includes two triple ring seals and a stabilizing ring shipped inside the block for easier storage. End caps sold separately.

TIMKEN

The Timken team applies their know-how to improve the reliability and performance of machinery in diverse markets worldwide. The company designs, makes and markets high-performance mechanical components, including bearings, belts, chain, gears and related mechanical power transmission products and services.

Stronger. Commitment. Stronger. Value. Stronger. Worldwide. Stronger. Together. | Stronger. By Design.

www.timken.com

150 06-15 :29 Order No. 10848 | Timken® is a registered trademark of The Timken Company. | © 2015 The Timken Company | Printed in U.S.A.