

Bearing Isolator Pump Sizes



Pump No.	I/O	Dimensions (inches)	Product Code		
			Non-Metallic (Glass-Filled PTFE)	Metallic	Non-Metallic (Graphite-Filled PTFE)
Goulds 3138S	Inboard	2.125 x 3.000	29502-4205	29602-4205	24802-1323
	Outboard	1.875 x 2.686	29502-4330	29602-4330	24807-2834
Goulds 3138MX	Inboard	2.875 x 4.000	29502-4331	29602-4331	24802-2843
	Outboard	2.625 x 3.484	29502-4332	29602-4332	24802-2844
Goulds 3139S	Inboard	2.125 x 3.000	29502-4205	29602-4205	24802-1323
	Outboard	1.875 x 2.686	29502-4330	29602-4330	24807-2834
Goulds 3139MX	Inboard	2.875 x 4.000	29502-4331	29602-4331	24802-2843
	Outboard	2.625 x 3.484	29502-4332	29602-4332	24802-2844
Goulds 3145S	Inboard	Not Available			
	Outboard	2.375 x 3.250	29502-4112	29602-4112	24802-1581
Goulds 3171L	Outboard	1.875 x 5.000	29502-4729	29602-4729	
Goulds 3171M	Outboard	1.375 x 3.625	29502-4730	29602-4730	
Goulds 3171S	Outboard	0.875 x 2.750	29502-4731	29602-4731	
Goulds 3175L	Inboard	4.313 x 5.500	29502-4115	29602-4115	24802-2700
	Outboard	4.125 x 5.250	29502-4116	29602-4116	24802-2605
Goulds 3175M	Inboard	3.312 x 4.125	29502-4113	29602-4113	24802-2296
	Outboard	3.125 x 4.125	29502-4114	29602-4114	24802-2223
Goulds 3175S	Inboard	2.500 x 3.250	29502-4111	29602-4111	24802-0991
	Outboard	2.375 x 3.250	29502-4112	29602-4112	24802-1581
Goulds 3175XL	Inboard	5.000 x 6.250	29502-4203	29602-4203	24802-2923
	Outboard	4.313 x 5.500	29502-4115	29602-4115	24802-2700
Goulds 3180L	Inboard	70mm x 95mm	29502-4192	29602-4192	
	Outboard	70mm x 95mm	29502-4192	29602-4192	
Goulds 3180M	Inboard	Not Required			
	Outboard	48mm x 70mm	29502-4189	29602-4189	24802-1935
Goulds 3180S	Inboard	55mm x 80mm	29502-4190	29602-4190	24802-2005
	Outboard	48mm x 70mm	29502-4189	29602-4189	24802-1935
Goulds 3180LX	Inboard	Not Required			
	Outboard	85mm x 110mm	29502-4193	29602-4193	24802-5650
Goulds 3185L	Inboard	70mm x 95mm	29502-4192	29602-4192	
	Outboard	85mm x 110mm	29502-4193	29602-4193	24802-5650
Goulds 3185M	Inboard	Not Required			
	Outboard	60mm x 85mm	29502-4191	29602-4191	
Goulds 3185S	Inboard	55mm x 80mm	29502-4190	29602-4190	24802-2005
	Outboard	48mm x 70mm	29502-4189	29602-4189	24802-1935
Goulds 3185XL	Inboard	Not Required			
	Outboard	85mm x 110mm	29502-4193	29602-4193	24802-5650
Goulds 3196ST	Inboard	1.375 x 2.835	29502-4104	29602-4104	24802-1138
	Outboard	0.875 x 1.250	29507-4106	29607-4106	24807-3196
Goulds 3196STX	Inboard	1.375 x 2.835	29502-4104	29602-4104	24802-1138
	Outboard	0.875 x 1.250	29507-4106	29607-4106	24807-3196

Pump No.	I/O	Dimensions (inches)	Product Code		
			Non-Metallic (Glass-Filled PTFE)	Metallic	Non-Metallic (Graphite-Filled PTFE)
Goulds 3196M	Inboard	1.750 x 2.875	29502-4107	29602-4107	24802-0998
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0998
Goulds 3196MT	Inboard	1.750 x 2.875	29502-4107	29602-4107	24802-0998
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0998
Goulds 3196MTX	Inboard	1.750 x 2.875	29502-4107	29602-4107	24802-0998
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0998
Goulds 3196LTC	Inboard	2.125 x 2.875	29502-4109	29602-4109	24802-1332
	Outboard	1.875 x 2.750	29502-4110	29602-4110	24802-1075
Goulds 3196LTX	Inboard	2.125 x 2.875	29502-4109	29602-4109	24802-1332
	Outboard	1.875 x 2.750	29502-4110	29602-4110	24802-4110
Goulds 3196XLT	Inboard	2.500 x 3.250	29502-4111	29602-4111	24802-0991
	Outboard	2.375 x 3.250	29502-4112	29602-4112	24802-1581
Goulds 3198MTX	Inboard	1.750 x 2.875	29502-4107	29602-4107	24802-0998
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0988
Goulds 3198STX	Inboard	1.375 x 2.835	29502-4104	29602-4104	24802-1138
	Outboard	0.875 x 1.250	29507-4106	29607-4106	24807-3196
Goulds 3296S	Inboard	Not Required			
	Outboard	0.875 x 1.250	29507-4106	29607-4106	24807-3196
Goulds 3316L	Inboard	1.937 x 3.000	29502-4120	29602-4120	24802-1123
	Outboard	2.062 x 3.000	29502-4119	29607-4119	24802-1225
Goulds 3316M	Inboard	1.437 x 2.437	29502-4177	29602-4177	24802-1116
	Outboard	1.375 x 2.125	29502-4118	29602-4118	24802-1092
Goulds 3316S	Inboard	1.062 x 1.643	29502-4206	29607-4206	24807-4389
	Outboard	0.937 x 1.500	29507-4122	29607-4122	24807-2563
Goulds 3316ST	Inboard	1.062 x 1.643	29507-4121	29607-4121	24807-3907
	Outboard	0.937 x 1.500	29507-4122	29607-4122	24807-2563
Goulds 3375S	Inboard	1.125 x 1.562	29507-4334	29607-4334	24807-2852
	Outboard	Not Available			
Goulds 3375ST	Inboard	1.125 x 1.562	29507-4334	29607-4334	24807-2852
	Outboard	Not Required			
Goulds 3405L	Inboard	1.937 x 3.000	29502-4120	29602-4120	24802-1123
	Outboard	2.062 x 3.000	29502-4119	29602-4119	24802-1225
Goulds 3405M	Inboard	1.437 x 2.437	29502-4177	29602-4177	24802-2720
	Outboard	1.375 x 2.125	29502-4118	29602-4118	24802-1092
Goulds 3405S	Inboard	1.062 x 1.643	29507-4206	29607-4206	24807-3907
	Outboard	0.937 x 1.500	29507-4122	29607-4122	24807-2563
Goulds 3410L	Inboard	2.187 x 3.000	29502-4204	29602-4204	24802-1119
	Outboard	2.187 x 3.000	29502-4204	29602-4204	24802-1119
	Inboard	2.125 x 3.000	29502-4205	29607-4205	24802-1323
Goulds 3410M	Inboard	1.375 x 2.835	29502-4104	29602-4104	24802-1138
	Outboard	1.500 x 2.125	29507-1118	29607-1118	24807-3410

Pump No.	I/O	Dimensions (inches)	Product Code		
			Non-Metallic (Glass-Filled PTFE)	Metallic	Non-Metallic (Graphite-Filled PTFE)
Goulds 3410S	Inboard	1.750 x 2.875	29502-4107	29602-4107	24802-0998
	Outboard	1.500 x 2.125	29507-1118	29607-1118	24807-3410
Goulds 3410XL	Inboard	2.187 x 3.000	29502-4204	29602-4204	24802-1119
	Outboard	2.187 x 3.000	29502-4204	29602-4204	24802-1119
	Inboard	2.125 x 3.000	29502-4205	29602-4205	24802-1323
Goulds 3420SX	Inboard	2.559 x 3.544	29502-4721	29602-4721	24802-1883
	Outboard	2.375 x 3.544	29502-4727	29602-4727	
Goulds 3700L	Inboard	3.149 x 4.135	29502-4728	29602-4728	24802-2272
	Outboard	2.625 x 3.625	29502-4151	29602-4151	24802-1841
Goulds 3700M	Inboard	2.437 x 3.437	29502-4280	29602-4280	24802-1641
	Outboard	2.186 x 3.186	29502-4279	29602-4279	24802-2489
Goulds 3700S	Inboard	2.280 x 3.280	29502-4338	29602-4338	24802-2312
	Outboard	2.186 x 3.186	29502-4279	29602-4279	24802-2489
Goulds 3700XL	Inboard	2.280 x 3.280	29502-4338	29602-4338	24802-2312
	Outboard	3.250 x 4.250	29502-4154	29602-4154	24802-2280
Goulds 3700X	Inboard	3.187 x 4.187	29502-4286	29602-4286	24802-2741
	Outboard	1.875 x 2.625	29502-4124	29602-4124	24802-0989
Goulds 3375M	Inboard	1.875 x 2.625	29502-4124	29602-4124	24802-0989
	Outboard	Not Available			
Goulds 3735L	Inboard	2.250 x 3.250	29502-4148	29602-4148	24802-1493
	Outboard	1.625 x 2.250	29507-4347	29607-4347	24807-2164
Goulds 3736M	Inboard	1.875 x 2.625	29502-4124	29602-4124	24802-0989
	Outboard	Not Available			
Goulds 3755MT	Inboard	1.625 x 2.625	29502-4144	29602-4144	24802-1089
	Outboard	1.625 x 2.625	29502-4144	29602-4144	24802-1089
Goulds 3755S	Inboard	1.125 x 1.562	29507-4334	29607-4334	24807-2852
	Outboard	Not Available			
Goulds 3796LTX	Inboard	2.125 x 2.875	29502-4109	29602-4109	24802-1322
	Outboard	1.875 x 2.750	29502-4110	29602-4110	24802-1075
Goulds 3796MT	Inboard	1.750 x 3.937	29502-4348	29602-4348	24802-3970
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0988
Goulds 3796MTX	Inboard	1.750 x 3.937	29502-4348	29602-4348	24802-3970
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0988
Goulds 3796STX	Inboard	1.375 x 2.875	29502-4104	29602-4109	24802-1135
	Outboard	0.875 x 1.250	29502-4106	29602-4110	24807-3196
Goulds 3996LTX	Inboard	2.125 x 2.875	29502-4109	29602-4109	24802-1322
	Outboard	1.875 x 2.750	29502-4110	29602-4110	24802-1075
Goulds 3996M	Outboard	1.750 x 2.875	29502-4107	29602-4107	24802-0998
	Outboard	1.375 x 2.125	29502-4118	29602-4118	24802-1092
	Inboard	1.250 x 2.000	29502-4185	29602-4185	24802-1215
Goulds 3996MT	Inboard	1.750 x 3.937	29502-4348	29602-4348	24802-3970
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0988

Bearing Isolator Pump Sizes

Product Code					
Pump No.	I/O	Dimensions (inches)	Non-Metallic (Glass-Filled PTFE)	Metallic	Non-Metallic (Graphite-Filled PTFE)
Goulds 3996MTX	Inboard	1.750 x 3.937	29502-4348	29602-4348	24802-3970
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0988
Goulds 3996S	Inboard	1.375 x 2.125	29502-4118	29602-4118	24802-1092
	Outboard	1.375 x 1.875	29507-4176	29607-4176	24807-2512
Goulds 3996ST	Inboard	1.375 x 2.835	29502-4104	29602-4104	24802-1138
	Outboard	0.875 x 1.250	29507-4106	29607-4106	24807-3196
Goulds 3996STX	Inboard	1.375 x 2.835	29502-4104	29602-4104	24802-1138
	Outboard	0.875 x 1.250	29507-4106	29607-4106	24807-3196
Goulds LF96MTX	Inboard	1.750 x 3.937	29502-4348	29602-4348	
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0988
Goulds JC/HS/5150-C1	Outboard	2.312 x 4.500	29502-4732	29602-4732	
Goulds JC/HS/5150-C2	Outboard	3.500 x 6.500	29502-4733	29602-4733	
Goulds JC/HS/5150-C3	Outboard	4.688 x 8.750	29502-4734	29602-4734	
Goulds JC/HS/5150-C4	Outboard	5.500 x 10.250	29502-4735	29602-4735	
Goulds JC/HS/5150-C5	Outboard	6.625 x 10.500	29502-4736	29602-4736	
Goulds JC/HS/5150-C5A	Outboard	6.625 x 8.750	29502-4737	29602-4737	
Goulds JC/HS/5150-C6	Outboard	7.750 x 11.250	29502-4738	29602-4738	
Goulds JC/HS/5150-C6A	Outboard	7.750 x 10.500	29502-4739	29602-4739	
DURCO MKII GRP I	Inboard w/o	1.125 x 2.441	29502-4181	29602-4181	24802-2859
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0988
DURCO MKII GRP III	Inboard	0.875 x 1.625	29507-4123	29607-4123	24802-1012
	Outboard	2.625 x 3.677	29502-4125	29602-4125	24802-1086
DURCO MKIII GRP I	Inboard	2.625 x 3.677	29502-4125	29602-4125	24802-1086
	Outboard	1.375 x 2.835	29502-4104	29602-4104	24802-1138
DURCO MKIII GRP II	Inboard	0.875 x 1.625	29507-4123	29602-4123	24802-1012
	Outboard	1.875 x 2.625	29502-4124	29602-4124	24802-0989
DURCO MKIII GRP II (oversized shaft)	Inboard	1.125 x 2.000	29502-4108	29602-4108	24802-0988
	Outboard	1.875 x 2.625	29502-4124	29602-4124	24802-0989
DURCO MKIII GRP III	Inboard	1.500 x 2.000	29502-4130	29602-4130	24802-2578
	Outboard	2.625 x 3.677	29502-4125	29602-4125	24802-1086
ITT-AC CSO, F4-A1	Inboard	2.625 x 3.677	29502-4125	29602-4125	24802-1086
	Outboard	1.000 x 1.750	29502-4182	29602-4182	24807-2695
ITT-AC CSO, F4-B2	Inboard	1.000 x 1.750	29502-4182	29602-4182	24807-2695
	Outboard	1.750 x 2.375	29507-4183	29607-4183	24807-2200
ITT-AC CSO, F4-B3	Inboard	1.125 x 1.750	29507-4184	29607-4184	24807-2994
	Outboard	1.250 x 2.000	29502-4185	29602-4185	24802-1215

Product Code					
Pump No.	I/O	Dimensions (inches)	Non-Metallic (Glass-Filled PTFE)	Metallic	Non-Metallic (Graphite-Filled PTFE)
ITT-AC CSO, F4-B3	Inboard	1.750 x 2.375	29507-4183	29607-4183	24807-2200
	Outboard	1.125 x 1.750	29507-4184	29607-4184	24807-2994
ITT-AC CSO, F4-C1	Inboard	1.250 x 2.000	29502-4185	29602-4185	24802-4185
	Outboard	1.375 x 2.125	29502-4118	29602-4118	24802-2858
ITT-AC CSO, F4-D1	Inboard	1.000 x 1.750	29502-4182	29602-4182	24807-2695
	Outboard	1.250 x 1.750	29502-4109	29602-4109	24802-1322
ITT-AC CSO, F8-E1	Inboard	1.250 x 1.750	29507-4340	29602-4340	24807-1782
	Outboard	3.250 x 4.000	29502-4186	29602-4186	24802-1028
ITT-AC PWO, F8-B1	Inboard	2.750 x 3.500	29502-4187	29602-4187	24802-1238
	Outboard	2.750 x 3.500	29502-4186	29602-4186	24802-1028
ITT-AC PWO, F8-B2	Inboard	2.750 x 3.500	29502-4187	29602-4187	24802-1238
	Outboard	3.250 x 4.000	29502-4186	29602-4186	24802-1028
ITT-AC PWO, F8-B4	Inboard	2.750 x 3.500	29502-4187	29602-4187	24802-1238
	Outboard	4.500 x 5.500	29502-4165	29602-4165	24802-2755
ITT-AC PWO, F8-C1	Inboard	3.750 x 4.750	29502-4158	29602-4158	24802-2464
	Outboard	3.250 x 4.000	29502-4186	29602-4186	24802-1028
ITT-AC PWO, F8-M1	Inboard	2.750 x 3.500	29502-4187	29602-4187	24802-1238
	Outboard	3.250 x 4.000	29502-4186	29602-4186	24802-1028
ITT-AC PWO, F9-B1	Inboard	2.750 x 3.500	29502-4187	29602-4187	24802-1238
	Outboard	3.250 x 4.000	29502-4186	29602-4186	24802-1028
ITT-AC PWO, F9-M1	Inboard	2.750 x 3.500	29502-4187	29602-4187	24802-1238
	Outboard	2.750 x 3.250	29502-4148	29602-4148	24807-4792
ITT-AC PW-CW, FR1	Inboard	1.875 x 2.625	29502-4124	29602-4124	24802-0989
	Outboard	3.187 x 4.187	29502-4286	29602-4286	24807-2741
ITT-AC PW-CW, FR2	Inboard	2.750 x 3.500	29502-4187	29602-4187	24802-1238
	Outboard	4.500 x 5.500	29502-4165	29602-4165	24807-2755
ITT-AC PW-CW, FR3	Inboard	4.187 x 5.250	29502-4366	29602-4366	24802-2646
	Outboard	2.250 x 3.190	29502-4367	29602-4367	24802-1901
ITT-AC PWO, F8-L1	Inboard	1.750 x 2.625	29502-4323	29602-4323	24802-1062
	Outboard	4.500 x 5.500	29502-4165	29602-4165	24802-2755
ITT-AC PWO, F8-N1	Inboard	3.750 x 4.750	29502-4158	29602-4158	24802-2464
	Outboard	2.250 x 3.190	29502-4367	29602-4367	24802-1901
ITT-AC PWO, F9-L1	Inboard	1.750 x 2.625	29502-4323	29602-4323	24802-1062
	Outboard	4.500 x 5.500	29502-4165	29602-4165	24802-2755
ITT-AC PWO, F8-N1	Inboard	3.750 x 4.750	29502-4158	29602-4158	24802-2464
	Outboard	2.246 x 4.500	29502-4368	29602-4368	
ITT-AC 8 X 6 SKD	Inboard	2.246 x 4.500	29502-4368	29602-4368	
	Outboard	2.246 x 4.500	29502-4368	29602-4368	
ITT-AC Y	Inboard	4.625 x 5.625	29502-4166	29602-4166	24802-2808
	Outboard	3.750 x 4.750	29502-4158	29602-4158	24802-2464
Peerless 8175L	Inboard	4.312 x 5.500	29502-4115	29602-4115	24802-2700
	Outboard	3.375 x 4.125	29502-4385	29602-4385	24807-3767
Peerless 8175M	Inboard	3.312 x 4.125	29502-4113	29602-4113	24802-2296
	Outboard	3.125 x 4.125	29502-4114	29602-4114	24802-2223

Product Code					
Pump No.	I/O	Dimensions (inches)	Non-Metallic (Glass-Filled PTFE)	Metallic	Non-Metallic (Graphite-Filled PTFE)
Peerless 8175S	Inboard	2.500 x 3.250	29502-4111	29602-4111	24802-0991
	Outboard	2.375 x 3.250	29502-4112	29602-4112	24802-1581
Peerless 8196LTC	Inboard	2.125 x 2.875	29502-4109	29602-4109	24802-1322
	Outboard	1.875 x 2.750	29502-4110	29602-4110	24802-1075
Peerless 8196MT	Inboard	1.750 x 2.875	29502-4107	29602-4107	24802-0998
	Outboard	1.125 x 2.000	29502-4108	29602-4108	24802-0988
Peerless 8196ST	Inboard	1.375 x 2.835	29502-4104	29602-4104	24802-1138
	Outboard	0.875 x 1.250	29507-4106	29607-4106	24807-3196
Peerless 8196XLT	Inboard	2.500 x 3.250	29502-4111	29602-4111	24802-0991
	Outboard	2.375 x 3.250	29502-4112	29602-4112	24802-1581
Warren #11 MARK I	Inboard	4.500 x 5.750	29502-4391	29602-4391	24802-2761
	Outboard	3.500 x 4.375	29502-4214	29602-4214	24802-2378
Warren #11 MARK II	Inboard	5.000 x 6.000	29502-4391	29602-4169	24802-2917
	Outboard	3.500 x 4.375	29502-4214	29602-4214	24802-2378
Warren #125 MARK I	Inboard	5.250 x 6.750	29502-2573	29602-2573	24802-3073
	Outboard	4.000 x 5.375	29502-4209	29602-4209	24802-2633
Warren #125 MARK II	Inboard	5.875 x 7.125	29502-4211	29602-4211	24802-3324
	Outboard	4.000 x 5.375	29502-4209	29602-4209	24802-2633
Warren #135 MARK I	Inboard	6.250 x 7.750	29502-3405	29602-3405	24802-2253
	Outboard	4.750 x 6.000	29502-4218	29602-4218	24802-2875
Warren #135 MARK II	Inboard	6.250 x 7.750	29502-3405	29602-3405	24802-2253
	Outboard	4.500 x 6.000	29502-4212	29602-4212	24802-2767
Warren #8 MARK I	Inboard	2.875 x 4.125	29502-4215	29602-4215	24802-2001
	Outboard	2.000 x 3.125	29502-4217	29602-4217	

Note:

29502 - 0.750" wide 29602 - 0.700" wide 24802 - 0.625" wide
 29507 - 0.625" wide 29607 - 0.625" wide 24807 - 0.625" wide

Distributed by The Timken Company. Timken® Service Parts are carefully chosen from select manufacturers. Keep clean and dry.