

TIMKEN® PERFORMANCE RACING GREASE
Lubricating Grease**Part Numbers**

GR246C 400 g (14 oz) cartridge

Handling and Storage

Store in a dry area away from heat and open flame. See Material Safety Data Sheet for more information.

Shipping and Disposal Information

Follow governmental regulations pertaining to the shipping and disposal of this product. Do not reuse container after use. See Material Safety Data Sheet for more information.

TIMKEN® PERFORMANCE RACING GREASE
Product Specifications – Typical

Color	Ivory
NLGI Grade	No. 2
Thickener Type	Lithium Complex
Penetration, Unworked, ASTM D 217	265-295
Penetration, Worked 60 Strokes, ASTM D 217	280
Penetration Change, 100000 Strokes, ASTM D 217	+/- 5 %
Wheel Bearing, ASTM D 1263	5 Grams Max.
Dropping Point, ASTM D 2265	265° C Min.
Oxidation Stability, ASTM D 942, 100 hours at 99° C	5 psi
Four-Ball Wear, ASTM D 2266, 40 kg, 1200 RPM, 75° C, Scar mm	0.50 Max.
Four-Ball EP, Weld Point, ASTM D 2596, kgf	315 Min.
Timken OK Load, ASTM D 2509, Pounds	55
Copper Strip Corrosion, ASTM D 4048	1b
Corrosion Preventive Properties, ASTM D 1743	Pass
Oil Separation, ASTM D 1742	2 % Max.
Base Fluid Properties:	
Viscosity @ 100° C, ASTM D 445, Centistokes	25
Viscosity @ 40° C, ASTM D 445, Centistokes	207

Product Data Sheet

TIMKEN®

Viscosity Index	143
Pour Point, ASTM D 97	- 45°C
Flash Point, ASTM D 92	>230° C

Date: June 19, 2026

Product: TIMKEN Performance Racing Grease