TIMKEN












AFTERMARKET SOLUTIONS FOR:

- TRUCKS
- TRAILERS
- BUSES

INDEX



Stay on the road longer 4

One worldwide quality standard 5

Trucks 6

Trailers 20

Buses 22

Wheel-Pac™ Repair Kits 27

Automatic lubrication kits for fifth wheel and tail lift 30

STAY ON THE ROAD LONGER

HERITAGE

Since Henry Timken patented the tapered roller bearing in 1898, The Timken Company has been **recognized as a worldwide leader in the manufacturing of highly engineered bearings**. Timken also has an impressive history of designing related friction management products.

AFTERMARKET

Timken serves the medium-duty and commercial vehicle aftermarket, with engineered products and technical resources **designed to maximize reliability, uptime and performance** – helping you stay on the road longer.

BROAD LINE OF PRODUCTS


- Tapered roller bearings
- Unit bearings
- Ball bearings
- Premium wheel hub units
- Seals
- Repair kits
- Maintenance tools
- Lubrication systems

+12,000
PART NUMBERS
interchangeable with OE and competitors brands

A BRAND YOU CAN TRUST

You can trust Timken because **we deliver products with reliable operation and outstanding performance** designed to enhance fleet uptime, operations and financial performance.





PART COVERAGE
for the Top 7 CV brands



ONE WORLDWIDE QUALITY STANDARD

Timken has only one set of worldwide quality standards and every facility, employee and supplier must adhere to them. Engineered for reliable operation, long life and outstanding performance, only tested, proven and genuine Timken products bear our name.

DATA
Every Timken designer, engineer and manufacturing employee uses the same design, production and assembly data.

TRAINING
We train our associates, so they know how to achieve consistent product quality.

EQUIPMENT
We check and test all equipment to help ensure product consistency and quality.

DIMENSIONAL ACCURACY
We achieve consistent dimensional accuracy of our products with precision gauging and calibration systems.

HIGH-QUALITY STEEL
We use only high-quality steel that meets our strict standards, and we test it to verify proper chemistry, cleanness, case hardness and depth.

Because our quality standards are so strict, **we've played a major role establishing industry standards for bearing quality** – for both the International Organization for Standardization (ISO) and the American Bearing Manufacturers Association (ABMA).

TRUCKS



MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
DAF						
65	SET1304, SET1049		SET1079, SET361	SET1303		SET1091
65 CF	SET1304, SET1049		SET1079, SET1080, SET361	SET1093, SET1341, SET1303, 681A/672		SET405, SET1091, SET1308
75	SET1304		SET1079, SET1080	SET1304, SET1303, 681A/672, SET1093		SET1308, SET1079, SET1091, SET405
75 CF	SET1304	SET2351, SET2346	SET1079, SET1080	SET1341, SET1093, SET1303, 681A/672, SET1304	SET2352	SET1308, SET405, SET1091, SET1079
85	SET1304		SET1080, SET1079	SET1093, SET1303, SET1304, 681A/672		SET1308, SET1091, SET1079, SET405
85 CF	SET1304	SET2351, SET1348, SET2346	SET1079, SET1080	SET1341, SET1093, SET1303, 681A/672, SET1304	SET2352	SET405, SET1308, SET1091, SET1079
95	SET1304		SET1079, SET1080, SET1078	SET1093, SET1303, 681A/672, SET1304		SET1308, SET1091, SET405, SET1079
95 XF	SET1304		SET1079, SET1080	SET1304, 681A/672, SET1303, SET1093		SET1308, SET1079, SET1091, SET405
CF 65	SET1304	SET2346, SET2351	SET1079, SET1080	SET1303, 681A/672, SET1341, SET1093	SET2352	SET1308, SET1091, SET405

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
DAF						
CF 75	SET1304	SET1348, SET2351, SET2346	SET1079, SET1080	SET1303, SET1341, SET1093, 681A/672	SET2352	SET1308, SET405, SET1091
CF 85	SET1304, SET1061	SET2346, SET1348, SET2351	SET1079, SET1080, SET1108	681A/672, SET1341, SET1303, SET1093, SET1061, SET1308	SET2352	SET405, SET1308, SET1091, SET1108, SET1093
F 1000	SET416		SET1119	SET325		SET1178
F 1300						SET1331
F 1500	SET1081, SET1093, SET244, SET1163	SET1231	SET1052, SET1078, SET1333	SET317, SET1067, SET1065, SET1308, SET414		SET1308, SET317, SET414, SET1067, SET1064, SET1115
F 1600	SET278, 5583/5535, SET1300		SET406, SET1079, SET102	SET404, 681A/672		SET1129, SET405
F 1700	SET1078		SET1078			
F 1800	SET1138		SET262	681A/672		SET405
F 1900			32309B			
F 2000	SET1300, 6379/6321, 5583/5535		SET1110, SET1079, SET406	681A/672		SET1129, SET405
F 2100	5583/5535, SET1300		SET406, SET1110, SET1079	681A/672, SET508		SET1130, SET405
F 2200	6379/6321		SET406, SET1079	SET109, SET508, 681A/672		SET405, SET922, SET1130
F 2300	SET1300		SET1079, SET1110	SET508, 681A/672		SET1130, SET405
F 2500	SET1300		SET1079	681A/672, SET508, SET1341		SET405, SET1130
F 2700	SET1300		SET1079	SET1303		SET1091
F 2800	SET1300		SET1079, SET1110	681A/672, SET508		SET1130, SET405
F 2900	SET1300		SET1079	SET1303, SET1341		SET1091
F 3200	SET1300		SET1079	681A/672, SET1341		SET405
F 3300	SET1300		SET1079	SET508, 681A/672		SET1130, SET405

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
DAF						
F 3600	SET1300		SET1079	SET1341, SET1303		SET1091
F 600	SET1109		SET1055	SET1125		
F 800	SET1109		SET1055	SET1125		
LF 45	SET1177, SET416, SET278	SET2351	SET1119, SET1055	SET1093, SET1046, SET1125	SET2352	SET98, SET1308, SET1125, SET1307
LF 55	SET114, SET1304	SET2351, SET2346	SET1079, SET1109	SET1303, SET1049, SET1125	SET2352, SET1242	SET1091, 495/493, SET1125
N 2800	SET1300		SET1079	SET508		SET1130
XF		SET2346, SET1348			SET2352	
XF 105	SET1061	SET1348, SET2346, SET2351	SET1108	SET1093	SET2352	SET1308
XF 95	SET1304, SET1061	SET1348, SET2346, SET2351	SET1079, SET1080, SET1108	SET1303, 681A/672, SET1341, SET1093, SET1061	SET2352	SET1091, SET1308, SET405, SET1108
IVECO						
EuroCargo I-III	SET1195, SET1031, SET1111, SET1201, SET1051, SET1091, SET1200		SET1199, SET1030, SET1111, SET1201, SET1091, SET1051, SET1208, SET1048	SET1293, SET1100, SET1207, SET349, SET1286, SET1026, SET1024, SET1287, SET1134, SET1104, SET1091	SET1263, SET1237, SET1242	SET1293, SET1100, SET1207, SET98, SET325, SET1024, SET1026, SET1286, SET1104, SET1134, SET1051, SET1287, SET1115
EuroFire	SET1195, SET1091, SET1111		SET1199, SET1051, SET1111	SET1293, SET1024, SET1207	SET1237	SET1293, SET1026, SET1207, SET325
EuroStar	SET1200		SET1208	SET1069, SET1070, SET1200, SET1287, SET1067	SET1242	SET1286, SET1068, SET1208, SET1066
EuroTech MH	SET1200, SET1287		SET1208, SET1286	SET1070, SET1200	SET1242	SET1286, SET1208

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
IVECO						
EuroTech MP	SET1200, SET1307		SET1208	SET1287, SET1070, SET1067, SET1026, SET1069, SET1200	SET1242	SET1286, SET1066, SET1053, SET1068, SET1208
EuroTech MT	SET1200		SET1208	SET1287, SET1070	SET1242	SET1286
EuroTrakker	SET1091, SET1200, SET1051		SET1208, SET1051, SET1091	SET1026, SET1053, SET1287		SET1026, SET1053, SET1286
M	SET1112, 6386/6320		SET1111, SET1079	SET1286, SET1287, SET1068		SET325, SET1286, SET1066
MK	SET1059, SET1030, SET1031, SET1022, XAA33212, SET1060, SET1058		SET349, SET1031, SET1056, SET1030, SET1109, SET1134, SET1057, SET1055	SET1179, SET349, SET1022, SET1047, SET1100		SET98, SET349, SET1064, 47487/47420, SET1100
P/PA	SET115, SET1051, SET1091, SET1032, 6386/6320		SET1080, SET1091, SET1051, SET1078, SET1079	SET1053, SET1026, SET1024, SET1080, SET1068		SET1026, SET1091, SET1053, SET1066
P/PA-Hauben-fahrzeuge	SET1091, SET115, SET1051, SET1200, SET1022, SET1079		SET1051, SET1080, SET1091, SET1208, SET1134, SET1076	SET1026, SET1053, SET1080, SET1022, SET1024		SET1053, SET1026, SET1064
Stralis	SET1200		SET1208	SET1200	SET1242	SET1208
Trakker	SET1200, SET1091		SET1208, SET1051	SET1026	SET1242	SET1053, SET1026
TurboStar	SET115		SET1080	SET1070		SET1286
TurboTech	SET115		SET1080	SET1070, SET1053		SET1026, SET1286, SET1080

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
MAN						
Zeta	SET1031, SET1195, SET1296		SET1030	SET1044, SET1100, SET1293, SET349, SET1286		SET1044, SET1100, SET1293, SET98, SET325
CLA		SET1336				SET1025
E 2000	SET1300, XGA32021X	SET1336	SET1049, SET1079, SET1092, SET1309	SET1341, XGA32021X, SET1300		SET1025, SET1309, SET1049, SET1091, SET1079, SET1092
F 2000	SET1300, XGA32021X, SET1325, SET1332, SET1047	SET1336	SET1079, SET1056, SET1109, SET1078, SET1045, SET1049, SET1091, SET1025	SET1300, SET1341, SET1049, SET1024, SET1324, SET1094, SET1047		SET1025, SET1091, SET1045, SET1309, SET1101, SET408, SET1049, SET1079, SET1308
F 90	SET1300, XGA32021X, SET1049		SET1079, SET1049, XGA32021X	SET1049, SET1341, SET1300		SET1091, SET1309, SET1049, SET1025, SET1079
F 90 Unterflur	SET1300		SET1079	SET1341, SET1300		SET1025, SET1049, SET1091, SET1079
G	SET1060, SET1019, SET1134, SET1047		SET1055, SET1056, SET1047	SET1088, SET1324, SET325, SET1134, SET1047		3984/3927X, SET279, SET1047
G 90	SET1325		SET1055, SET1056	SET1324		SET408
L 2000	SET1300, SET1325, SET1332, SET1047, XGA32021X, HM220149Z/ HM220110Z, SET414	SET1337	SET1079, SET1078, SET1109, SET1056, SET1107, SET1106, SET1045, SET1049, HM220149Z/ HM220110Z	SET1343, SET1024, SET1047, SET1324, SET1064, SET1341, SET1048, SET1308, SET414	SET1263, SET2335	SET1045, SET1049, SET1101, SET1089, SET1091, SET408, SET1048, SET1107, SET1064, SET1308, SET414

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
MAN						
M 2000 L	SET1325, SET1047, XGA32021X, SET1332, SET1300, SET1298, SET1024	SET1336, SET1337	SET1049, SET1078, SET1079, SET1107, SET1045, SET1056, SET1109, SET1091, SET1101	SET1300, SET1094, SET1324, SET1047, SET1343, SET1024, SET1064, SET1341, XGA32021X, SET1048, SET1049	SET2335	SET1101, SET1049, SET1025, SET408, SET1091, SET1089, SET1045, SET1079, SET1048, SET1309, SET1064, SET1308
M 2000 M	SET1300, SET1332, XGA32021X, SET1047, SET1079	SET1336	SET1078, SET1079, SET1045, SET1049, SET1056, SET1109	SET1047, SET1300, SET1324, SET1094, SET1024, SET1064, SET1341, SET1048, SET1049	SET2335	SET1045, SET1091, SET1049, SET1025, SET1079, SET1101, SET408, SET1048, SET1309, SET1064
M 90	SET1298, SET1047, SET1332, SET1300, XGA32021X		SET1109, SET1057, SET1045, SET1078, SET1079, SET1049	SET1024, SET1064, SET1341, SET1049, SET1300, SET1332		SET1101, SET1048, SET1049, SET1091, SET1309, SET1078, SET1079
TGA	SET1117, XGA32021X	SET1336, SET2335	SET1023, SET1049, SET1091	SET1094, XGA32021X, SET1309, SET1025	SET2335, SET1336	SET1308, SET1309, SET1025, SET1049
TGL		SET1337			SET1263, SET1321	
TGM	XGA32021X	SET1337, SET1336, SET1263	SET1049		SET2335, SET1321, SET1336	SET1308
TGS	XGA32021X, SET1117	SET1336	SET1023, SET1049, SET1091		SET2335, SET1336	SET1309, SET1308

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
MERCEDES-BENZ						
TGX	SET1117	SET1336	SET1023	XGA32021X	SET2335, SET1336	SET1309, SET1091
ACTROS	SET115, SET1301, SET1083, SET1307, SET1328, SET1117, SET1330, SET1080, SET1091, SET1079, XGA32021X	SET1310	SET1080, SET1079, SET1081, SET1091, XGA32021X, SET1301, SET1302	SET1092, SET1093, SET1094, SET1307, SET1302		SET1309, SET1081, SET1102, SET1050, SET1302, SET1373, SET1049, SET1025
ACTROS MP2 / MP3	SET1083, SET115, SET1117, SET1307, SET1328, SET1301, XGA32021X, SET1094	SET1310, SET1349	SET1080, SET1081, SET1079, SET1091, SET1373, SET1302	SET1094, SET1092, SET1093, SET1309, SET1307	SET1310	SET1302, SET1102, SET1309, SET1050, SET1081, SET1373, SET1049, SET1025, SET1094
ACTROS MP4		SET1310		SET1094	SET1310	SET1302, SET1102
ANTOS		SET1310	SET1302	SET1094, SET1092	SET1310	SET1302, SET1102
AROCS	XGA32021X	SET1310	SET1091	SET1094, SET1092	SET1310	SET1302, SET1309, SET1102
ATEGO	SET1375, SET1098, SET1113, SET1343, SET1092, SET115, SET1307, SET1301, SET1091, SET1083, SET1117, SET1328, SET1330, SET1080	SET1349, SET1262	SET1074, SET1107, SET1108, SET1047, XGA32021X, SET1080, SET1079, SET1081, SET1091	SET1091, SET1092, SET1343, SET401, SET1102, SET1093, SET1094, SET1307	SET1365, SET1262	SET1086, SET1048, SET1102, SET1088, 39586/39528, SET1050, SET317, SET1309, SET1081, SET1302, SET1373

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
MERCEDES-BENZ						
ATEGO 2	SET1375, SET1113, SET1092, SET1343, SET1114, SET1107, SET1074, SET1307, SET1328	SET1349, SET1262, SET1263, SET1310	SET1074, SET1107, SET1108, SET1047, SET1110	SET1343, SET1092, SET401, SET1091, SET1375, SET1093, SET1094	SET1365, SET1262	SET1088, SET1102, 39586/39528, SET1048, SET1107, SET1074, SET1373, SET1081, SET1309, SET1302, SET1050
ATEGO 3	SET1343, SET1092	SET1262	SET1047	SET1092, SET1091		SET1102, SET1048
AXOR	SET1328, SET1307, XGA32021X, SET1301, SET1117, SET1083	SET1310	SET1081, SET1091, SET1079, SET1080	SET1094, SET1093, SET1083, SET1117, SET1307, SET1092, SET1091		SET1373, SET1302, SET1050, SET1080, SET1081, SET1102, SET1309, SET1115
AXOR 2	XGA32021X, SET1307, SET1083, SET1117, SET1301, SET1328, SET1091, SET1330, SET115, SET1081, SET1094	SET1310, SET1349	SET1081, SET1080, SET1091, SET1079, XGA32021X	SET1093, SET1094, SET1307, SET1092, SET1091	SET1310	SET1373, SET1050, SET1309, SET1302, SET1081, SET317, SET1102, SET1115
ECONIC	SET1307	SET1310	SET1081	SET1094, SET1093		SET1050, SET1302
ECONIC 2		SET1310		SET1094	SET1310	SET1302

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
MERCEDES-BENZ						
LK/LN2	SET1098, SET1041, SET1097, SET1113, SET1111, SET1343, SET1114, SET1301, XGA32021X, SET1091		SET1074, SET1055, SET1105, SET1323, SET1108, SET1109, SET1079, SET1049, SET1110, 39586/39528, SET1047, SET1103	SET325, SET1044, SET98, SET1066, SET928, SET1065, SET401, SET1046, SET1103, SET1326, SET1091, 39586/39528, 598/592A, SET1092, SET1093, SET1094		SET1086, SET1041, SET272, SET1330, 39586/39528, SET1327, SET1098, SET1063, SET1048, SET1115, SET1102, SET1064, SET1103, SET1049, SET1025, SET1309, SET1117, SET1301
MK	SET1113, SET1092, SET1091, SET208, SET1301, SET1083, SET1114, SET1093, SET1034		SET1108, SET1047, SET1079, 39586/39528, SET1110	SET1092, SET1093, SET1094, SET1066, SET1049, SET1091, SET1301		SET1103, SET1049, SET1091, SET1063, SET1309, SET1025, SET1115, SET1079
NG	SET1111, SET1113, SET208, SET1091, SET1114, SET1093, SET1343, SET1301, SET1083, SET1330, SET115, SET1117, SET330		39586/39528, SET1108, SET1074, SET1047, SET1110, SET1079, SET1049, SET1091, XGA32021X, SET1080	SET1066, SET401, SET1093, SET1092, SET1091, SET1094, SET1309, SET1025, SET1301, SET1051		39586/39528, SET1063, SET1103, SET1049, SET1115, SET1309, SET1117, SET1091, SET1025, SET1079, SET1110, SET401

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
MERCEDES-BENZ						
SK	XGA32021X, SET1083, SET1114, SET1301, SET115, SET1307, SET1117, SET1080, SET1113, SET1034, SET1079, SET317	SET1231	SET1110, SET1080, SET1079, SET1049, SET1091, SET1108, SET1109, SET1326, SET1083, SET1111, SET1025, SET317	SET1094, SET1092, SET1093, SET1301, SET1091, SET1113, SET1326, SET1049, SET1309, SET1050, SET1308, SET414		SET1025, SET1103, SET1091, SET1049, SET1302, SET1050, SET1115, SET1079, SET1309, SET1110, SET1093, SET1108, SET1094, SET1308, SET414
ZETROS	XGA32021X		SET1091	SET1094		SET1302, SET1309
RENAULT TRUCKS						
C	SET1114, 594/593X, SET1113		SET1109, SET1297, 594/593X, SET1110, SET1066	SET1169, SET1166, 52375/52618, SET1049, SET1113, SET109		64432/64708, SET109, SET1116, 52375/52618
G	SET1112, SET1113, SET1114		SET1097, SET1109, SET1110, SET1297, SET1113	SET1166, SET1169, SET414		SET1116, 64432/64708, SET1103, SET1191, SET1113
Kerax	SET1166	SET1350, SET1340, SET2312, SET2312	SET1191, SET1116	SET1166, SET1049	SET2312, SET2312, SET2314	SET1191, SET1116, SET1103
Magnum		SET1340, SET1350, SET2312, SET2312, SET1311		SET1049, SET1166, SET414	SET2312, SET2312, SET2314	SET1191, SET1103, SET1116, SET1113, SET1166
Major	SET1114	SET1340	SET1297	SET1166, SET1169, SET414		SET1116, 64432/64708, SET1191, SET1113

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
RENAULT TRUCKS						
Manager	SET1113, SET1114, 594/593X		SET1109, SET1297, SET1110, 594/593X, SET1066, SET1025	SET1166, SET1049, SET1169, SET414		SET1191, 64432/64708, SET1116, SET1113, SET1103
Maxter	SET1166, SET1049, 594/593X, SET1114, SET1113	SET1340	SET1191, SET1116, 594/593X, SET1297, SET1109, SET1110	SET1166, SET1049, SET1169		SET1116, SET1191, SET1103, 64432/64708
Midliner	SET1111, SET1110, SET1109, SET1113, SET1047, SET1048, SET1052, SET1114	SET1364	SET1109, SET1108, SET1107, SET1106, SET1110, SET1048, SET1047, SET1052, SET1297	SET1045, SET1089, 594/593X, SET1088, SET1166, SET1049, JLM714149P/ JLM714110P, SET324, SET1048, SET1047, SET1090		594/593X, SET1043, SET1047, SET1232, SET1087, SET1116, SET1103, SET1048, SET1066, SET1141, SET1089
Midlum	SET1048	SET1364, SET1338, SET1350	SET1047	SET324, JLM714149P/ JLM714110P, SET1047, SET1049		SET1043, SET324, SET1103, SET1116, JLM714149P/ JLM714110P
Premium		SET1350, SET1340		SET1049, SET1166	SET1340, SET1350	SET1103, SET1116, SET1191
Premium 2		SET2312, SET2312, SET1311		SET1166	SET2314, SET2312, SET2312	SET1103, SET1191, SET1116
R	SET1114, SET1063	SET1340	SET1109, SET1297	SET1166, SET1169, SET109, SET414		52375/52618, SET1116, 64432/64708, SET1113, SET1191

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
SCANIA						
2 - series	HM220149Z/ HM220110Z, SET244, SET1081, SET1093, SET1163, SET1080	SET1231	HM220149Z/ HM220110Z, SET1333, SET1078, SET1052, SET1076	SET317, SET414, SET1051, SET1067, SET1308, SET1065, SET1163, SET1184, SET244, SET1081	SET1231	SET1115, SET1308, SET1064, SET1067, SET414, SET1184, SET317, SET1333, SET1078, SET1051
3 - series	SET244, SET1081, SET1093, SET1163	SET1231	SET1078, SET1052, SET1333	SET1308, SET1065, SET1067, SET414, SET317, SET1163, SET244, SET1081		SET414, SET1064, SET1308, SET1115, SET317, SET1067, SET1333, SET1078
4 - series	HM220149Z/ HM220110Z	SET1231	HM220149Z/ HM220110Z	SET1308, SET414, SET1065, SET244	SET1231	SET1308, SET414, SET1115, SET1333
P,G,R,T - series	HM220149Z/ HM220110Z	SET1231	HM220149Z/ HM220110Z	SET1308, SET414	SET1231	SET414, SET1308
VOLVO						
F 10	6386/6320, SET244		SET212, SET276, SET1113	SET109, SET414, SET317, SET244, SET1068, SET216, SET113		SET1068, SET276, SET1113, SET414, SET922, SET405, SET401
F 12	6386/6320, SET244		SET212, SET276	SET317, SET244, SET113, SET216, SET1068, SET109, SET414		SET276, SET1113, SET401, SET1068, SET414, SET922, SET405
F 16	SET244		SET276	SET244, SET317, SET109		SET414, SET276, SET405, SET922
F 4	SET1059		SET1056, SET1055	SET1088, SET1058		SET1087

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
VOLVO						
F 6	SET1059, SET1060, SET1176, SET244, 6386/6320		SET1056, SET1057, SET315, SET212, SET276	SET1089, SET216, SET1090		SET1232, SET401, SET1089
F 7	6386/6320, SET244		SET212, SET276	SET109, SET113, SET216, SET244		SET405, SET1113, SET401, SET276
F 80	6386/6320		SET212	SET109, SET216, SET1068		SET401, SET405, SET1068
FE		SET1311, SET2312, SET2312			SET2314, SET2312, SET2312	
FH		SET1311, SET2312, SET2312			SET2314, SET2312, SET2312, SET1311	
FH 12	SET244, SET1117	SET2312, SET1311, SET2312	SET276, SET1081	SET317, SET109	SET2312, SET2314, SET1311, SET2312	SET414, SET276, SET405
FH 16	SET1117, SET244	SET1311, SET2312, SET2312	SET1081, SET276	SET244, SET109, SET317	SET2314, SET1311, SET2312, SET2312	SET414, SET276, SET405
FH II		SET2312, SET2312, SET1311			SET2314, SET2312, SET2312, SET1311	
FL		SET1350		SET1049		SET1116, SET1103
FL 10	SET1117, SET244		SET1081, SET276, SET1112	SET317, SET244, SET109	SET2314	SET414, SET405, SET276
FL 12	SET244, SET1117		SET276, SET1081	SET109, SET244	SET2314	SET276, SET405
FL 6	SET244		SET1108, SET1107, SET276	SET1128, SET109, SET1090, SET244, SET216, SET208	SET2314	SET1101, SET405, SET408, SET401, SET276, SET1048
FL 7	SET244		SET276	SET317, SET109, SET244	SET2314	SET405, SET276, SET414

TRUCKS

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
VOLVO						
FL II		SET1350		SET1049		SET1103, SET1116
FL III		SET1350		SET1049		SET1103
FLC			SET1107	SET1088		SET1087
FM		SET2312, SET1311, SET2312			SET2314, SET1311, SET2312, SET2312	
FM 10	SET1117, SET244	SET2312, SET2312	SET1081, SET276	SET317, SET244	SET2314	SET414, SET276
FM 12	SET244, SET1117	SET2312, SET1311, SET2312	SET276, SET1081, SET272	SET109, SET317, SET244	SET2314, SET2312, SET1311, SET2312	SET414, SET276, SET405
FM 7	SET1117, SET244	SET2312, SET2312	SET1081, SET276	SET317, SET244	SET2314	SET414, SET276
FM 9	SET244	SET2312, SET1311, SET2312	SET276	SET244, SET317	SET2314, SET1311, SET2312, SET2312	SET414, SET276
FS 7	SET244		SET276	SET244, SET109, SET216		SET276, SET401, SET405
N 10	6386/6320, SET244		SET1076, SET276, SET212	SET109, SET216, SET1068		SET401, SET405, SET1068, SET414, SET922
N 7	6386/6320, SET244		SET1076, SET212, SET276	SET216, SET109		SET401, SET405
NH 12	SET244	SET2312, SET2312	SET276	SET317, SET109, SET244	SET2314	SET414, SET276, SET405

TRAILERS



MAKE	Inner	Outer	Other
Model			
BPW			
EH	SET1115	SET1079	
H	SET1068, SET1313, SET1102, SET1104, SET1115	SET1115, SET1114, SET1079, SET1113	SET1104
KH	SET1104, SET1102, SET1115, SET1068	SET1113, SET1079, SET1115	
KM	SET1115, SET1102, SET1104, SET1068	SET1079, SET1113, SET1115	
KR	SET1104, SET1102, SET1115, SET1068	SET1113, SET1079, SET1115	
M	SET1104	SET1113	
NH	SET1115, SET1102, SET1104	SET1079, SET1113	
NR	SET1068, SET1104, SET1102, SET1115	SET1115, SET1113, SET1079	
NRD	SET1068, SET1104	SET1115, SET1113	
R	SET1115, SET1102, SET1104, SET1068	SET1079, SET1113, SET1115	
SH	SET1104, SET1102	SET1113, SET1079	
SKH	SET1104, SET1102	SET1113, SET1079	
ZR		SET1113	SET1117
GIGANT			
Protec	SET1063	SET1113, SET1067, SET1069, SET1065	SET1310, SET1108, SET1104, SET1069
MERCEDES-BENZ			
NR		SET1080	SET1117
TE			SET1310
MERITOR			
TA	SET414	SET1113	
TE	SET1316	SET1315	
TM	SET414, SET1069	SET1113, SET1067	
ROCKWELL			
RS	SET105	SET404, SET401	

TRAILERS

MAKE	Inner	Outer	Other
Model			
SAF			
B			SET1370
EBN	SET1111, SET1100	SET1109, SET1031	SET1107, SET1030, SET1112
ES		SET1031	
ESN		SET1031	SET1030
EZN	SET1033	SET1031	
RBM	SET414, SET113	SET1113	
RLBM	SET414	SET1113	
RLSM	SET414	SET1113	
RS		SET1031	
RSM	SET414, SET113	SET1113, SET1100	
RZM	SET414, SET1067	SET1113, SET1083, SET1081	SET1070
RZT		SET1083	SET1070
S			SET1370
SK			SET1372
SKRB			SET1334, SET1369
SKRLB			SET1334
SKRLS			SET2371
SKRLZ			SET2371
SKRS			SET1372
SKRZ			SET1372
WESN	SET1033	SET1031	
WEZN	SET1033	SET1031	
WRLZM	SET414	SET1113	
WRZM	SET414, SET113	SET1113, SET1100	SET414
Z			SET1370
SCHMITZ CARGOBULL			
ROTOS			SET1334
SMB			
O	SET1299	SET1299	

BUSES



MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
BOVA						
Futura	SET1301		SET1078		SET2335	
Lexio	SET1307		SET1081		SET2335	
Magiq	SET1307		SET1081	SET1307	SET2335	SET1081
Synergy	SET1307		SET1081	SET1307	SET2335	SET1081
IRISBUS						
ARWAY		SET1350			SET1242, SET1257	
CITELIS		SET1350			SET2335	
CREALIS					SET2335	
CROSSWAY		SET1350			SET1242, SET1257	
DAILY TOURYS		SET1360			SET1368	
DOMINO	SET1200		SET1208		SET1242	
EVADYS		SET1350			SET1257, SET1242	
MAGELYS		SET1350			SET1257, SET1242	
PROWAY	SET1195		SET1199		SET1257	
RECREO		SET1350			SET1257	
IVECO						
City Class	SET1200		SET1208		SET1257	
URBANWAY		SET1350				
Zeta	SET1031		SET1030	SET1044, SET1100		SET1100
KING LONG						
XMQ	SET1024		SET1026	SET1024		SET1026
MAN						
EL	SET1300		SET1079	SET1341		SET1049
EM			SET1057	SET1024		SET1025, SET1101
FOCL		SET1337			SET1321	

BUSES

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
MAN						
G	SET1060		SET1056	SET325, SET1324, SET1088		3984/3927X, SET279
G 90	SET1325		SET1056	SET1324		SET408
HOCL	SET1332	SET1336	SET1109	SET1024	SET2335, SET1336	SET1101, SET1025
L 2000	SET1300, SET1325, SET1332		SET1079, SET1078, SET1109, SET1056, SET1107	SET1047, SET1024, SET1324, SET1343		SET1045, SET1101, SET408, SET1049, SET1091, SET1089
LION S CITY	SET1332	SET1336	SET1109	SET1341, SET1024	SET2335	SET1091, SET1101
LION S COACH	SET1300	SET1336	SET1079	SET1341	SET1336, SET2335	SET1091
LION S COMFORT		SET1336			SET2335, SET1336	
LION S STAR	SET1300	SET1336	SET1079	SET1341	SET2335, SET1336	SET1091
NG	SET1300	SET1336	SET1079	SET1341	SET2335	SET1049, SET1091
NL	SET1300	SET1336	SET1079	SET1341	SET2335	SET1091, SET1049
NM	SET1300	SET1336	SET1057, SET1079	XGA32021X, SET1024, SET1341	SET2335	SET1025, SET1101, SET1091
NÜ		SET1336		SET1341	SET2335, SET1336	SET1091
SG	SET1300		SET1110, SET1059, SET1079	SET1341		SET1049
SL	SET1300		SET1110	SET1341		SET1049
SL II	SET1300	SET1336	SET1079, SET1110, SET1059	SET1093	SET2335	SET1049, SET1025
SM			SET1057	SET1024		SET1025, SET1101
SR	SET1300		SET1110	SET1341		SET1049
SÜ	SET1300	SET1336	SET1110, SET1079	SET1093, SET1341	SET2335	SET1049, SET1091, SET1025

BUSES

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
MERCEDES-BENZ						
ÜL	SET1300	SET1336	SET1079	SET1341	SET2335	SET1091
CITARO (O 530)	SET1307, SET1301	SET1310	SET1081, SET1079	SET1307, SET1094	SET2335	SET1081
CONECTO (O 345)	SET1301		SET1079	SET1093	SET2335	SET1051, SET1049
INTEGRO (O 550)	SET1307	SET1310	SET1081	SET1094, SET1307		SET1081, SET1302
INTOURO	SET1307	SET1310	SET1081	SET1094		SET1302
LK/LN2	SET1111, SET1098, SET1113		SET1074, SET1323, SET1108	SET325, SET1046, SET1326, SET401, SET1063, SET1103, SET1091, 39586/39528		SET1330, SET1086, SET1327, 39586/39528, SET1063, SET1329
O 301	SET1113, SET1057, SET1111, SET1097, SET231		SET1105, SET1108, SET1072, SET226, SET1323	SET1060, SET98, SET1046		SET1059, SET272, SET1327
O 302	SET1114		SET1323, SET1110	SET1091, SET1092		SET1103, SET1115, 598/592A, SET1064
O 303	SET1114, SET1113, SET231, SET1057, SET1097, SET1111, SET1110, SET1109, SET1301		SET1110, SET1109, SET1108, SET1079, SET1072, SET226, SET1105, SET1323	SET1091, SET1065, SET1060, SET98, SET1092		39586/39528, SET1059, SET272, SET1103, SET1115
O 305	SET1301		SET1110, SET1079	SET1093		SET1049
O 307	SET1301		SET1110, SET1079	SET1093		SET1049
O 309	SET231, SET1113, SET1057, SET1097, SET1111, SET1056, SET98		SET1105, SET1072, SET226, SET1323, SET1108, SET272	SET98, SET1060		SET1059, SET272
O 317	SET1034		SET1079	SET1068, SET1115		SET1091, SET1066

BUSES

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
MERCEDES-BENZ						
O 340	SET1301		SET1079, SET1110	SET1094, SET1092		SET1103
O 402	SET1301, SET1111		SET1323, SET1079	SET1046		SET1327
O 403	SET1307		SET1088, SET1110	SET1092, SET1094		SET1103, SET1302
O 404	SET1307, SET1111, SET1301		SET1323, SET1079, SET1110	SET1092		SET1103
O 405	SET1301		SET1079, SET1110	SET1093		SET1049
O 407	SET1111, SET1301		SET1323, SET1110, SET1079	SET1093		SET1049
O 408	SET1301, SET1111		SET1079, SET1110, SET1323	SET1093		SET1049
OF Series	SET1098		SET1323	SET1326		SET1086
TOURINO (O 510)		SET1262		SET1092		SET1102
TOURISMO (O 350)	SET1307	SET1310	SET1110, SET1079, SET1081	SET1092, SET1094, SET1307	SET1310	SET1103, SET1302, SET1081
TOURO (O 500)	SET1307, SET1301		SET1081, SET1079	SET1094, SET1092		SET1081, SET1302, SET1102
TRAVEGO (O 580)	SET1307	SET1310	SET1081	SET1094, SET1307		SET1302, SET1081
NEOPLAN						
Centroliner	SET1301		SET1078	SET1184		SET1051
Cityliner	SET1301		SET1078	SET1184	SET2335	SET1051
Euroliner	SET1301		SET1078		SET2335	
Skyliner	SET1301		SET1078	SET1184		SET1078, SET1051
Starliner	SET1301	SET1336	SET1078	SET1184	SET2335, SET1336	SET1051
RENAULT TRUCKS						
Agora				SET1166		SET1116
FR1	SET1114		32309B, SET1078, SET1297	SET1166		SET1116
Tracer				SET1166		SET1103, SET1116

BUSES

MAKE	FRONT			REAR		
Model	Inner	Packaged Solutions	Outer	Inner	Packaged Solutions	Outer
SCANIA						
3 - series bus	SET1081, SET1163		SET1078	SET1067, SET414		SET414, SET1067
K - series		SET1231		SET414, SET1184	SET2335, SET1231	SET414, SET1051
SETRA						
Series 400	SET1307		SET1081			
VAN HOOL						
T-Serie					SET1242	
VOLVO						
7700	SET244	SET2312, SET2312	SET276		SET2314, SET2335, SET2312, SET2312	
8500	SET244	SET2312, SET2312	SET276		SET2314, SET2335, SET2312, SET2312	
8700	SET244	SET2312, SET2312	SET276		SET2314, SET2335, SET2312, SET2312	
9700	SET244	SET2312, SET2312	SET276		SET2312, SET2312, SET2314	
9900	SET244	SET2312, SET2312	SET276		SET2312, SET2312, SET2314	
B 10	SET244, 6386/6320		SET212, SET276	SET109, SET244, SET405		SET405, SET276, SET244
B 12	SET244		SET276	SET244, SET109		SET276, SET405
B 6		SET2312, SET2312	SET1108		SET2314	SET408
B 7	SET244		SET276	SET109		SET405
B 9		SET2312, SET2312			SET2314, SET2312, SET2335, SET2312	



WHEEL-PAC™ REPAIR KITS FAST AND EASY TO INSTALL

Engineered to help improve your fleet's uptime, this integrated wheel end solution comes pre-assembled, pre-greased, pre-sealed and pre-adjusted.

KEEPING YOUR VEHICLE IN MOTION

We apply our deep knowledge of metallurgy, tribology and mechanical systems to improve the reliability and efficiency of equipment, and vehicles worldwide.

With more than 18,000 employees operating from 42 countries, our associates and our products keep industry in motion and make the world more productive.

EASY MOUNTING AND INSTALLATION

- User-friendly installation tools protect the bearings during transport and assembly.
- Color-coded inboard and outboard tools reduce the risk of incorrect mounting.
- Integrated seals help prevent mounting errors and reduce assembly time.
- Bore clip keeps the assembly intact and eases the hub removal process.
- Easy to understand graphical fitting instructions.

KIT COMPONENTS:

- **1 inboard bearing with grease shield and white mounting tool**
- **1 outboard bearing with grease shield and black mounting tool**
- **1 bore clip**
- **1 fitting instruction guide**

SET2311 58mm MAIN APPLICATIONS

Model	Axle Position	OEM PN
RENAULT TRUCKS		
Magnum Premium 2 K-Serie T-Serie	Front	74 20 967 830 74 20 518 617 74 21 021 381 74 21 022 433 75 21 022 434 76 21 024 188
VOLVO TRUCKS		
FE / FE II FH / FH II FH 12 FH 16/16 II FM FM 9 FM 12 FMX FMX II	Front Axle Rear Axle non driven	20518617, 20967830 10003570, 20523899, 20589393, 20589394 20818748, 21021381 21022433, 3099341

SET2312 68mm MAIN APPLICATIONS

Model	Axle position	OEM PN
RENAULT TRUCKS		
KERAX	Front	74 20 535 202, 74 20 535 203, 74 21 024 206, 74 21 024 208, 74 20 518 637, 74 20 967 831, 74 21 021 391
MAGNUM	Front	
PREMIUM 2	Front	
VOLVO TRUCKS		
FE	Front	3988673, 3988674, 3988675, 3988830, 20382168, 20518091, 20518092, 20518093, 20518637, 20558950, 20728008, 20967831, 21021391
FH	Front	
FH 12	Front	
FH 16	Front	
FM	Front	
FM 12	Front	
FM 7	Front	
FM 9	Front	
NH 12	Front	
VOLVO BUSES		
7700	Front	3988673, 3988674, 3988675, 3988830, 20382168, 20518091, 20518092, 20518093, 20518637, 20558950, 20728008, 20967831, 21021391
8500	Front	
8700	Front	
9700	Front	
9900	Front	
B6	Front	

SET2314 94mm MAIN APPLICATIONS

Model	Axle Position	OEM PN
RENAULT TRUCKS		
KERAX	Rear	50 01 861 915, 74 20 516 957, 74 20 518 661, 74 20 535 262, 74 20 535 263, 74 20 535 264, 74 20 792 439, 74 20 819 834, 74 20 819 846, 74 20 819 859, 74 20 819 860, 74 21 036 050
MAGNUM	Rear	
PREMIUM 2	Rear	
VOLVO TRUCKS		
FE	Rear	103444, 1075408, 1078053, 3943982, 3987673, 3988774, 3989896, 9955401, 20517163, 20517164, 20517950, 20517952, 20518054, 20518661, 20535230, 20535231, 20535244, 20535263, 20558966, 20792439, 20792440, 20820402, 20967828, 21036050, 21328181, 85104299, 85104301, 205352445
FH	Rear	
FH 12	Rear	
FH 16	Rear	
FH II	Rear	
FL 10	Rear	
FL 12	Rear	
FL 6	Rear	
FL 7	Rear	
FM	Rear	
FM 10	Rear	
FM 12	Rear	
FM 7	Rear	
FM 9	Rear	
NH 12	Rear	
VOLVO BUSES		
7700	Rear	103444, 1075408, 1078053, 3943982, 3987673, 3988774, 3989896, 9955401, 20517163, 20517164, 20517950, 20517952, 20518054, 20518661, 20535230, 20535231, 20535244, 20535263, 20558966, 20792439, 20792440, 20820402, 20967828, 21036050, 21328181, 85104299, 85104301, 205352445
8500	Rear	
8700	Rear	
9700	Rear	
9900	Rear	
B 6	Rear	
B 9	Rear	

WHEEL-PAC™

SET2346 70mm MAIN APPLICATIONS

Model	Axle Position	OEM PN
DAF		
75 CF	Front	1691621, 1697346, 1699327, 1801592, 1818004
85 CF	Front	
CF 65	Front	
CF 75	Front	
CF 85	Front	
LF 45	Front	
LF 55	Front	
XF 105	Front	
XF 95	Front	
VDL		
		41801592

SET2352 100mm MAIN APPLICATIONS

Model	Axle Position	OEM PN
DAF		
75 CF	Rear	1391617, 1391617, 165 7637, 1657637, 180 1594, 1801594, 181 2161, 1812161, 181 8003,1818003
85 CF	Rear	
CF 65	Rear	
CF 75	Rear	
CF 85	Rear	
LF 45	Rear	
LF 55	Rear	
XF 105	Rear	
XF 95	Rear	
VDL		
		41801594

SET2351 70mm MAIN APPLICATIONS

Model	Axle Position	OEM PN
DAF		
75 CF	Front	1388905, 1391615, 1801595, 1807595
85 CF	Front	
CF 65	Front	
CF 75	Front	
CF 85	Front	
LF 45	Front	
LF 55	Front	
XF 105	Front	
XF 95	Front	

SET2370 88mm MAIN APPLICATIONS

SAF TRAILER AXLES
OEM PN
03 200 1020 00 03 434 3020 00 03 434 3022 00

SET2371 100mm MAIN APPLICATIONS

Model	Axle Position	OEM PN
SAF		
SKRLS	SKRLS 9037	3 434 3011 00
	SKRLZ 11037	
	SKRLZ 9037	



GROENEVELD MULTILINE KITS



EASY-TO-INSTALL AUTOMATIC LUBRICATION:

Your own mechanic can install the Groeneveld automatic lubrication kits for fifth wheel and tail lift when and where you want!

EVERYTHING YOU NEED IN ONE INSTALLATION KIT

The kit contains everything you need for installation: instructions, schematics, injectors, pre-loomed tubing, connectors and adapters.

Installation time for the pump is about one hour with 15 minutes additional time per lubrication point.

Automatic lubrication applies grease in small doses at regular intervals evenly over the surface of the fifth wheel and tail lift.

A regularly-refreshed grease film helps keeps out dirt, dust and water.

Advantages of automatic vs. manual lubrication:

- Save time
- Prolong service life
- Reduce repairs and lower maintenance costs
- Improve vehicle uptime
- Cut grease consumption by up to 50%
- Protect your investment and resale value

GROENEVELD-BEKA
LUBRICATION SYSTEMS BY TIMKEN

SELF-INSTALL AUTOMATIC LUBRICATION KIT FOR TAIL LIFTS

Universal tail lift kit	
Part number	AC724
Reservoir sizes	2.0L
Lubrication points	19
Output per stroke	0.025 cc
Voltage	24V
Maximum working pressure	120 bar (12 MPa)
Maximum operation temperature	60 °C (140 °F)
Minimum operation temperature*	-23 °C (-10 °F) with Greenlube NLGI-0-grease. -13 °C (9 °F) with Greenlube NLGI-2 grease



* based on maximum lubricant distribution line length of 10m / 32ft.
Caution: Temperatures with use of non-Groeneveld greases cannot be guaranteed.

Grease options		
	Universal grease	**Low-temperature grease**
Description	Greenlube EP-2	Greenlube LT-00
Classification		
NLGI grade ASTM D217	2	00
DIN 51502	KP2K-20	KP00G-35
ISO 6743	ISO-L-XBCEB2	ISO-L-XCBIB00
Temperature range	-20 to +130°C	-35 to +100°C
Drum sizes	18 & 50 kg	18 & 50 kg



Universal tail lift kit & related parts	
Kit no.	**Kit description**
AC724	Universal tail lift kit (24V, 19 points, grease)
Part no.	**Spare part description**
AC2522-1	AC2522-1 replacement pump (24V, 24 outlet)
Part no.	**Lubricant description**
F210058	GV Greenlube EP-2 grease NLGI grade 2 – 18Kg steel pail
F210060	GV Greenlube EP-2 grease NLGI grade 2 – 50Kg steel drum
F210054	GV Greenlube LT-00 grease NLGI grade 00 – 18kg steel pail (low-temperature)
F210057	GV Greenlube LT-00 grease NLGI grade 00 – 50kg steel drum (low-temperature)
Part no.	**Accessories description**
F104562	Tube cutter
F178054	Manual hand-operated filler pump kit for 18kg steel pail – NLGI-00
F121623	Manual hand-operated filler pump kit for 18kg steel pail – NLGI-2

Installation video

Installation manual

SELF-INSTALL AUTOMATIC LUBRICATION KIT FOR FIFTH WHEELS

Universal fifth wheel kit	
Part number	AC741
Reservoir sizes	1.25L
Lubrication points	6
Output per stroke	0.025 cc
Voltage	24V
Maximum working pressure	120 bar (12 MPa)
Maximum operation temperature	60 °C (140 °F)
Minimum operation temperature*	-23 °C (-10 °F) with Greenlube NLGI-0-grease. -13 °C (9 °F) with Greenlube NLGI-2 grease



* based on maximum lubricant distribution line length of 10m / 32ft.
Caution: Temperatures with use of non-Groeneveld greases cannot be guaranteed.

Grease options		
	Universal grease	**Low-temperature grease**
Description	Greenlube EP-2	Greenlube LT-00
Classification		
NLGI Grade ASTM D217	2	00
DIN 51502	KP2K-20	KP00G-35
ISO 6743	ISO-L-XBCEB2	ISO-L-XCBIB00
Temperature range	-20 to +130°C	-35 to +100°C
Drum sizes	18 & 50 kg	18 & 50 kg



Universal fifth wheel kit & related parts	
Kit no.	**Kit description**
AC741	Universal fifth wheel kit (24V, 6 points, grease)
Part no.	**Spare part description**
AC1522-1	AC1521-1 Replacement pump (24V, 12 outlet)
Part no.	**Lubricant description**
F210058	GV Greenlube EP-2 grease NLGI grade 2 – 18kg steel pail
F210060	GV Greenlube EP-2 grease NLGI grade 2 – 50kg steel drum
F210054	GV Greenlube LT-00 grease NLGI grade 00 – 18kg steel pail (low-temperature)
F210057	GV Greenlube LT-00 grease NLGI grade 00 – 50kg steel drum (low-temperature)
Part no.	**Accessories description**
F104562	Tube cutter
F178054	Manual hand-operated filler pump kit for 18kg steel pail – NLGI-00
F121623	Manual hand-operated filler pump kit for 18kg steel pail – NLGI-2

Installation video

Installation manual

TIMKEN WHEEL END SOLUTIONS COVER 93% OF THE TRUCKS OPERATING IN EUROPE*

Contact a Timken sales representative today to discover how **we can help you stay on the road longer.**

TecAlliance
Certified Data Supplier

* % coverage based on TecAlliance VIO data for vehicles under 15 years of age, which Timken can supply at least one product for front and rear axles, for all makes and models, “unspecified N-types”

For more information, please visit our catalogs at:
TecDoc Catalog
https://web.tecalliance.net/tecdocsw/en/login

Commercial Vehicle Bearings Catalog
https://www.timken.com/resources/commercial-vehicle-bearing-catalog/

TIMKEN

The Timken team applies their know-how to improve the reliability and performance of machinery in diverse markets worldwide. The company designs, makes and markets bearings, gear drives, automated lubrication systems, belts, brakes, clutches, chain, couplings, linear motion products and related power transmission rebuild and repair services.

www.timken.com/aftermarket

Stronger. By Design.

?M 01-20: ?? Order No. E0420-GB | Timken® is a registered trademark of The Timken Company. | © 2020 The Timken Company | Printed in Europe