



OPERATE WITH **EXTENDED UPTIME**

Timken® Set-Right® Commercial Vehicle Hub Rebuild Kits

As a tapered roller bearing technology leader, Timken can help you increase your fleet's uptime and performance. Engineered to help increase fuel efficiency and simplify installation, Timken® Set-Right® Commercial Vehicle Hub Rebuild Kits are also available for severe duty and wide single tire applications.



Accurate Bearing Setting:

Timken® Set-Right® kits feature bearings that **significantly reduce the width variation** found in standard bearings. Our **tight bearing width tolerance enables consistent and accurate bearing setting** of pre-adjusted hubs.

Consistent Bearing Setting:

Consistently achieve proper wheel bearing setting, avoiding the need for manual bearing adjustment and **promoting optimum bearing and seal life**.

Streamlined Inventory

Management: With a **wide range of part numbers**, each kit features two Timken MileMate® matched bearing sets and a precision-machined spacer (**five common spacer types available**).

Longer Lasting Bearings Can Mean More Uptime. MileMate bearings, manufactured with super-clean, high-strength alloy steel, precision profiles and enhanced surface finishes, feature high load ratings, and **outlast and outperform competitor bearings.***

TIMKEN

*Based on 2012 comparison testing conducted with case-carburized bearings against top competitors. All bearings were commercially available and produced in North America. Information derived from Timken Standard Life Testing, using significant statistical samplings of bearings in a controlled test environment.

Set-Right® Commercial Vehicle Hub Rebuild Kits and Components

FFTC1 - FF Steer Kit			
Kit Contents	MileMate® P/N	Component P/N	Qty
Inner NP cone	SET427*	NP899357	1
Inner NP cup		NP026773	1
Outer NP cone	SET428*	NP874005	1
Outer NP cup		NP435398	1
Spacer		103592TKR	1

RDTC1 - R Drive Kit			
Kit Contents	MileMate® P/N	Component P/N	Qty
Inner NP cone	SET429*	NP034946	1
Inner NP cup		NP363298	1
Outer NP cone	SET430*	NP840302	1
Outer NP cup		NP053874	1
Spacer		103593TKR	1

TNTC1 - N Trailer Kit			
Kit Contents	MileMate® P/N	Component P/N	Qty
Inner NP cone	SET431*	NP965350	1
Inner NP cup		NP503727	1
Outer NP cone	SET427*	NP899357	1
Outer NP cup		NP026773	1
Spacer		104144TKR	1

TPTC1 - P Trailer Kit			
Kit Contents	MileMate® P/N	Component P/N	Qty
NP cone	SET432*	NP174964	2
NP cup		NP593561	2
Spacer		104412TKR	1



FLTC1 - FL Steer Kit			
Kit Contents	MileMate® P/N	Component P/N	Qty
Inner NP cone	SET445*	NP294109	1
Inner NP cup		NP039695	1
Outer NP cone	SET446*	NP107091	1
Outer NP cup		NP183330	1
Spacer		103807TKR	1

FFTC2 - 454-Series™ FF Steer Kit			
Kit Contents	MileMate® P/N	Component P/N	Qty
Inner NP cone	SET603*	NP454357	1
Inner NP cup		NP454773	1
Outer NP cone	SET605*	NP454005	1
Outer NP cup		NP454398	1
Spacer		103592TKR	1

RDTC2 - 454-Series™ R Drive Kit			
Kit Contents	MileMate® P/N	Component P/N	Qty
Inner NP cone	SET600*	NP454946	1
Inner NP cup		NP454298	1
Outer NP cone	SET601*	NP454302	1
Outer NP cup		NP454874	1
Spacer		103593TKR	1

TNTC2 - 454-Series™ N Trailer Kit			
Kit Contents	MileMate® P/N	Component P/N	Qty
Inner NP cone	SET602*	NP454350	1
Inner NP cup		NP454727	1
Outer NP cone	SET603*	NP454357	1
Outer NP cup		NP454773	1
Spacer		104144TKR	1

TPTC2 - 454-Series™ P Trailer Kit			
Kit Contents	MileMate® P/N	Component P/N	Qty
NP cone	SET604*	NP454964	2
NP cup		NP454561	2
Spacer		104412TKR	1



* Includes proprietary Timken part numbers

Contact a Timken sales representative today to discover how our Set-Right® Commercial Vehicle Hub Rebuild Kits can extend your fleet's uptime. (866) 9-TIMKEN (984-6536).

TIMKEN

The Timken team applies their know-how to improve the reliability and performance of machinery in diverse markets worldwide. The company designs, makes and markets bearings, gear drives, automated lubrication systems, belts, brakes, clutches, chain, couplings, linear motion products and related industrial motion rebuild and repair services.

Stronger. By Design.

www.timken.com/aftermarket