TIMKEN



BEARING SOLUTIONS FOR PEELERS/SCRUBBERS

ARE YOU REPLACING PEELER BEARINGS TOO OFTEN?

Every hour your peeler is down it costs you — lost production, extra labor, and frustration. Frequent bearing changes not only eat into maintenance budgets, but also disrupt schedules and put food safety at risk.


TIMKEN KEEPS YOUR PEELERS RUNNING LONGER

In food and beverage operations, peelers face some of the harshest conditions: frequent chemical washdowns, abrasive contaminants, and high-speed operation. Timken's broad portfolio of engineered solutions — from corrosion-resistant mounted ball bearings to advanced lubrication technologies — is built to perform in these environments. Our components are designed to deliver maximum uptime, longer service life, and consistent performance, helping you cut maintenance costs while keeping your lines running clean, safe, and efficient.

With decades of experience supporting leading OEMs and processors worldwide, Timken helps you meet strict food safety standards, extend equipment life, and protect your bottom line.



CARTRIDGE BEARING SOLUTIONS



Peeler/scrubber drive pack



TAPERED ROLLER BEARING CARTRIDGE UNIT

- Stainless steel cartridge and black-oxide-coated collars for corrosion resistance
- High-performance seals drastically reduce contaminant ingress compared to the leading competitor's seals
- Timken® tapered roller bearings for heavy loads
- Direct drop-in replacement for OEM bearings - comes filled with food grade grease
- Example Part-Number: E-MC-TRB-24144-FG

PLAIN BEARING CARTRIDGE UNIT


- Stainless steel cartridge and sleeve for corrosion resistance
- High-performance polymer bearing insert for lubricant-free operation
- Replaceable bearing insert for reduced maintenance costs
- Rebuildable design
- Direct drop-in replacement for OEM bearings
- Example Part-Number: EDT SGH



MOUNTED BEARING SOLUTIONS



Mounted solid-block bearing



Peeler/scrubber drive pack

CORROSION-RESISTANT MOUNTED UNITS

- Available in standard grease and solid-lubricated versions for reduced maintenance
- Fully stainless-steel housing and insert for enhanced corrosion resistance
- Housing configurations available in two-bolt, four-bolt, pillow block, and more
- Direct drop-in for OEM bearings
- Example Part-Number: SUCSFL206-19/F





SOLID-BLOCK MOUNTED SPHERICAL ROLLER BEARINGS

- Powder coated steel housing for increased durability
- Black-oxide-coated inner ring and locking hardware for corrosion resistance
- Stainless-steel options available
- Spherical roller bearing insert for high radial load and misalignment capability
- Housing configurations available in two-bolt, four-bolt, pillow block and more
- Example Part-Number: QAF08A108SM



LUBRICATION SOLUTIONS

Timken offers a wide range of lubrication solutions to meet your demands. From automated greasing systems to maintenance-free solid lubricant, Timken has the products to keep your peelers running smoothly.



Groeneveld-Beka Automatic Lubrication Systems



Timken Food Grade Solid Lube Options



Industrial Grease Options

TIMKEN FOOD AND BEVERAGE SUPPORT

- Timken Food and Beverage Website: www.timken.com/food
- Timken CAD Website: cad.timken.com
- Timken Engineering Tools Website: engineering.timken.com

TIMKEN

The Timken team applies their know-how to improve the reliability and performance of machinery in diverse markets worldwide. The company designs, makes and markets bearings, gear drives, automated lubrication systems, belts, brakes, clutches, chain, couplings, linear motion products and related industrial motion rebuild and repair services.

Stronger. By Design.

www.timken.com

10-25 Order No. 11837 POD | Timken® is a registered trademark of The Timken Company. | © 2025 The Timken Company | Printed in U.S.A.