



Product Data Sheet

TIMKEN® BALL BEARING PILLOW BLOCK GREASE Lubricating Grease

Part Numbers

GR220C	400 g (14 oz) cartridge
GR220F	1 kg (2.2 lb) tub
GR220G	5 kg (11 lb) pail
GR220P	16 kg (35.3 lb) pail
GR220K	55 kg (121.3 lb) keg
GR220D	180 kg (400 lb) drum

Product Description and Intended Use

TIMKEN Ball Bearing Pillow Block Grease is a NLGI No. 2 shear stable polyurea thickened grease specifically designed for the lubrication of moderate to high speed ball bearings in pillow block applications. TIMKEN Ball Bearing Pillow Block Grease is also recommended for the lubrication of high speed ball bearings in applications such as alternators, generators, starters, electric motors and other long life applications.

TIMKEN Ball Bearing Electric Motor Grease does not contain extreme pressure additives as required by many electric motor bearing manufacturers, and exhibits excellent corrosion resistance.

Product Application

TIMKEN Ball Bearing Pillow Block Grease can be applied from ambient temperatures of - 30° F to + 325° F (- 34° C to + 163° C) depending on lubrication system design and method of application. TIMKEN Ball Bearing Pillow Block Grease has an operating range of - 40° F to + 325° F (- 40° C to + 163° C) once in the application. Follow equipment manufacturer's recommendations concerning lubrication frequencies.

Compatibility of Grease

TIMKEN Ball Bearing Pillow Block Grease is generally compatible with calcium sulfonate, polyurea, lithium soap, and lithium complex thickened greases. Timken recommends that all grease be removed from the application prior to changing greases. Then the lubrication interval is reduced by half for the first lubrication cycle before resuming the normal lubrication interval.

Handling and Storage

Store in a dry area away from heat and open flame. See Material Safety Data Sheet for more information.

Shipping and Disposal Information

Follow governmental regulations pertaining to the shipping and disposal of this product. Do not reuse container. See Material Safety Data Sheet for more information.

TIMKEN® BALL BEARING PILLOW BLOCK GREASE

Product Specifications – Typical

Color	Dark Blue
NLGI Grade	2
Thickener Type	Polyurea
Penetration, Unworked, ASTM D 217	220 Min.
Penetration, Worked 60 Strokes, ASTM D 217	265-295
Penetration Change, 100000 Strokes, ASTM D 217	310-360
Wheel Bearing Leakage, ASTM D 1263	5 Grams Max.
Dropping Point, ASTM D 2265	> 260° C
Oxidation Stability, ASTM D 942, 100 hours at 99° C	5
Four-Ball Wear, ASTM D 2266, 40 kg, 1200 RPM, 75° C, Scar mm	0.4
Copper Strip Corrosion, ASTM D 4048	1a
Corrosion Preventive Properties, ASTM D 1743	Pass
EMCOR Corrosion, ASTM D 6138, 10 % Synthetic Seawater	0,0
Oil Separation, ASTM D 1742	0.3
Water Washout, ASTM D 1264, 175° F (79° C), % Loss	2
Bearing Life, ASTM D 3336, 177° C, Hours	> 750
Base Fluid Properties:	
Viscosity @ 100° C, ASTM D 445, Centistokes	9-13
Viscosity @ 40° C, ASTM D 445, Centistokes	100-120
Viscosity Index	95
Flash Point, ASTM D 92	255° C
Pour Point, ASTM D 97	- 15° C

Date: November 18, 2008

Product: TIMKEN Ball Bearing Pillow Block Grease