



## STRONG, NON-CORROSIVE SOLUTIONS. DURABLE APPLICATIONS.

### TIMKEN® SOLID-BLOCK MOUNTED SPHERICAL ROLLER BEARINGS WITH STAINLESS STEEL HOUSINGS

When strength and versatility matter most, Timken Solid-Block Mounted Spherical Roller Bearings are the answer.

On the outside, the rugged housing of Timken Solid-Block Mounted Spherical Roller Bearings is engineered from cast stainless steel to withstand the harshest conditions. The units are unaffected by washdown and stand up to process moisture and chemical sanitation.

On the inside, these durable, versatile mounted bearings feature six primary seals in any combination, plus an optional secondary seal. The black oxide inner ring reduces shaft fretting corrosion. Applications ideal for this product include pulp and paper processing to waste water, marine and food and beverage processing.





### VERSATILE DESIGN OPTIONS

- Optically and metal detectable urethane covers available
- Available in 2-bolt and 4-bolt pillow blocks and 4-bolt flange block housing styles
- Single or double collar set screw locking
- Stainless
  - Housing
  - NU Nuts
  - Hardware
  - Collar
- Size Range 1 7/16 – 4 in. (35 – 100 mm)




# SOLID-BLOCK MOUNTED SPHERICAL ROLLER BEARINGS WITH STAINLESS STEEL HOUSING




## COVER NOMENCLATURE

### OPEN END-END COVER WITH DR SEAL



### CLOSED-END COVER



## CALL ON TIMKEN

For your nearest Timken sales representative, visit [www.timken.com](http://www.timken.com)

# TIMKEN

The Timken team applies their know-how to improve the reliability and performance of machinery in diverse markets worldwide. The company designs, makes and markets bearings, gear drives, automated lubrication systems, belts, brakes, clutches, chain, couplings, linear motion products and related industrial motion rebuild and repair services.

**Stronger. By Design.**

[www.timken.com](http://www.timken.com)