

EXPANDED U SERIES OFFERING
TIMKEN® U SERIES BALL BEARING HOUSED UNITS

Our line of standard and heavy-duty U Series Ball Bearing Housed Units includes Set Screw Locking (UC 200 and UC 300), Eccentric Locking Collar (UEL 200) and Tapered Bore for use with Adapter Sleeve Locking Series (UK 200) and provides reliable Timken products readily available for the most popular applications.

INCREASED EQUIPMENT UPTIME AND REDUCED MAINTENANCE COST

- Bearings with spherical outer rings and precision-machined cast-iron housings help prevent outer ring rotation.
- Bearings withstand static misalignment of the shaft of +/–3 degrees.
- Designed for normal operation between –20° C and 100° C (–4° F and 212° F).
- Wide inner ring bearings deliver greater shaft support.
- High-strength housings suited for most industrial applications.
- Bearings are prelubricated and ready for immediate installation.
- Timken knowledge and support come standard.

ROBUST SEALING PERFORMANCE IN THE MOST DEMANDING ENVIRONMENTS

- Precision sealing provides extended bearing life and reduced lubrication leakage.
- Bonded seal design includes a steel flinger for additional bearing protection.
- Effective grease retention and reduced debris and moisture ingress improve bearing performance.

WIDE RANGE OF READY-TO-MOUNT UNITS

- Six different housing designs plus replacement inserts are offered in metric and imperial sizes.
- Set screw locking, tapered bore for use with adapter sleeve and eccentric locking collar design allow for easy installation.
- Extensive range of sizes meets the needs of a wide range of applications.
- Interchangeable without modification in many applications.
- Regional in-stock availability ensures the service levels you expect.



PILLOW BLOCK UNITS
UCP – 12 mm to 140 mm (½ in. to 4 in.)
UKP – 20 mm to 80 mm (¾ in. to 3 in.)
UELP – 12 mm to 75 mm (½ in. to 3 in.)



TAKE-UP UNITS
UCT – 12 mm to 140 mm (½ in. to 4 in.)
UKT – 20 mm to 75 mm (¾ in. to 3 in.)
UELT – 12 mm to 75 mm (½ in. to 3 in.)



TWO-BOLT FLANGED UNITS
UCFL – 12 mm to 130 mm (½ in. to 4 in.)
UKFL – 20 mm to 80 mm (¾ in. to 3 in.)
UELFL – 12 mm to 75 mm (½ in. to 3 in.)



TAPPED BASE PILLOW BLOCK UNITS
UCPA – 12mm to 50mm (½ in. to 2 in.)
UELPA – 12mm to 50mm (½ in. to 2 in.)
UKPA – 20mm to 45mm (¾ in. to 1¾ in.)
UCPW – 25mm to 40mm
UELPW – 25mm to 40mm



FOUR-BOLT FLANGED UNITS
UCF – 12 mm to 90 mm (½ in. to 3 ½ in.)
UELF – 12 mm to 75 mm (½ in. to 3 in.)
UKF – 20 mm to 80 mm (¾ in. to 3 in.)



WIDE INNER RING BALL BEARINGS
UC – 12 mm to 140 mm (½ in. to 4 in.)
UK – 20 mm to 80 mm (¾ in. to 3 in.)
UEL – 12 mm to 75 mm (½ in. to 3 in.)



PILOTED ROUND FLANGED UNITS
UCFC – 12 mm to 90 mm (½ in. to 3 ½ in.)
UKFC – 20 mm to 80 mm (¾ in. to 3 in.)
UELFC – 12 mm to 75 mm (½ in. to 3 in.)

NOMENCLATURE
CONFIGURATIONS TO MEET YOUR NEEDS

BALL HOUSED UNITS
Standard and heavy series – wide inner ring, set screw, tapered bore for use with adapter sleeve and eccentric locking collar mechanisms.

HOUSING TYPES
Pillow block, tapped base pillow block, two-bolt flange, four-bolt flange, piloted round flange and take-up.

METRIC BORE SIZES
12 mm – 140 mm

INCH BORE SIZES
½ in. – 4 in.

INDUSTRIES/APPLICATIONS

- **Materials Handling**
- **Food and Beverage**
- **Agriculture**
- **Packaging**
- **Industrial Fans/Blowers**
- **Glass Making**
- **Brick Making**
- **Paper and Printing**

UC P 2 05 - 16

Bearing Insert Code
UC – Set screw locking mechanism
UEL – Eccentric locking collar
UK – Tapered bore for use with adapter sleeve

Housing Code
P – Pillow block unit
F – Four-bolt flange unit
PA – Tapped base pillow block unit
PW – Y series tapped base pillow block unit
FL – Two-bolt flanged unit
T – Take-up unit
FC – Piloted round flanged unit


Series Code
2 – standard industrial series
3 – heavy-duty series

Metric Bore Diameter Code For Cylindrical Bore (1)
01 – Nominal bore diameter = 12 mm
02 – Nominal bore diameter = 15 mm
03 – Nominal bore diameter = 17 mm
04 or higher – Bore diameter (mm) = bore diameter code x 5
(1)For adapter UK style - refer to catalog tables for shaft diameter.

Example:
UCF201 = 12 mm bore (Four-bolt flanged unit)
UELP211 = 55 mm bore (Pillow block unit)

Inch Diameter Code
-8 or higher – Bore diameter (in.) = bore diameter code/16

Example:
UCF201-8 = 8/16 in. or ½ in. bore (Four-bolt flanged unit)
UCP205-16 = 16/16 in. or 1 in. bore (Pillow block unit)



TIMKEN

The Timken team applies their know-how to improve the reliability and performance of machinery in diverse markets worldwide. The company designs, makes and markets high-performance mechanical components, including bearings, belts, brakes, clutches, chain, couplings, gears and related mechanical power transmission products and services.

Stronger. By Design.

www.timken.com

Order No. E11111-GB | Timken® is a registered trademark of The Timken Company. | © 2023 The Timken Company | Printed in Europe.