



## STRONG, NON-CORROSIVE SOLUTIONS. DURABLE APPLICATIONS.

### TIMKEN® SPHERICAL ROLLER BEARING SOLID-BLOCK HOUSED UNIT

When strength and versatility matter most, Timken Spherical Roller Bearing Bearing Solid-Block Housed Unit is the answer.

On the outside, the rugged housing of Timken SRB Solid-Block Housed Units are engineered from cast stainless steel to withstand the harshest conditions. They are unaffected by washdown and stand up to process moisture and chemical sanitation.

On the inside, these durable, versatile housed units feature six primary seals in any combination, plus an optional secondary seal. The black oxide inner ring reduces shaft fretting corrosion. Applications ideal for this product include pulp and paper processing to waste water, marine and food and beverage processing. Pick the configuration right for your application.



#### VERSATILE DESIGN OPTIONS

- Available in 2-bolt QAP, 4-bolt QAAPF pillow blocks and 4-bolt flange (Type E) dimensions
- Single or double collar set screw locking
- Stainless
  - Housing
  - NU Nuts
  - Hardware
  - Collar

Size Range 1 $\frac{1}{16}$  - 4 in. (35 - 100 mm)



# SPHERICAL ROLLER BEARING SOLID BLOCK HOUSED UNIT WITH STAINLESS STEEL HOUSING



## TIMKEN

The Timken team applies their know-how to improve the reliability and performance of machinery in diverse markets worldwide. The company designs, makes and markets bearings, gear drives, automated lubrication systems, belts, brakes, clutches, chain, couplings, linear motion products and related power transmission rebuild and repair services.

Stronger. By Design.

## CALL ON TIMKEN

For your nearest Timken sales representative, visit [www.timken.com](http://www.timken.com)

[www.timken.com](http://www.timken.com)