

TIMKEN


SAFETY DATA SHEET

MILL GREASE NLGI 2

Section 1. Identification

Product identifier	: MILL GREASE NLGI 2
Other means of identification	: Not available.
Product type	: Solid.
Product code	: GR182.
SDS #	: 1744
Relevant identified uses of the substance or mixture and uses advised against	
Product use: For professional use only.	: Industrial applications: Lubricants; grease.
Supplier's details	: The Timken Corporation 4500 Mt. Pleasant St. NW North Canton, OH 44720 U.S.A. 234.262.3000
Emergency telephone number (with hours of operation)	: INFOTRAC U.S. and Canada - 800.535.5053 Outside the U.S. and Canada - +1 352.323.3500

Section 2. Hazard identification

Classification of the substance or mixture	: EYE IRRITATION - Category 2A SKIN SENSITIZATION - Category 1
GHS label elements	
Hazard pictograms	: 
Signal word	: Warning
Hazard statements	: Causes serious eye irritation. May cause an allergic skin reaction.
Precautionary statements	
Prevention	: Wear protective gloves. Wear eye or face protection. Avoid breathing dust. Wash hands thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace.
Response	: IF ON SKIN: Wash with plenty of soap and water. Take off contaminated clothing and wash it before reuse. If skin irritation or rash occurs: Get medical attention. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention.
Storage	: Not applicable.
Disposal	: Dispose of contents and container in accordance with all local, regional, national and international regulations.
Other hazards which do not result in classification	: None known.

Section 2. Hazard identification

Section 3. Composition/information on ingredients

Substance/mixture : Mixture
Other means of identification : Not available.
CAS number/other identifiers

Ingredient name	% (w/w)	CAS number
Distillates (petroleum), solvent-dewaxed heavy paraffinic	40-70	64742-65-0
Mineral Oil	10-30	-
Benzenesulfonic acid, C10-16-alkyl derivs.	3-7	68584-22-5
Sulfonic acids, petroleum, calcium salts	1-5	61789-86-4
diboron calcium tetraoxide	1-5	13701-64-9
calcium dodecylbenzenesulphonate	1-5	26264-06-2

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

Section 4. First-aid measures

Description of necessary first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 10 minutes. Get medical attention.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Get medical attention if adverse health effects persist or are severe. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.
- Skin contact** : Wash with plenty of soap and water. Remove contaminated clothing and shoes. Wash contaminated clothing thoroughly with water before removing it, or wear gloves. Continue to rinse for at least 10 minutes. Get medical attention. In the event of any complaints or symptoms, avoid further exposure. Wash clothing before reuse. Clean shoes thoroughly before reuse.
- Ingestion** : Wash out mouth with water. Remove dentures if any. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Get medical attention if adverse health effects persist or are severe. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

Most important symptoms/effects, acute and delayed

Potential acute health effects

- Eye contact** : Causes serious eye irritation.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : May cause an allergic skin reaction.
- Ingestion** : No known significant effects or critical hazards.

Over-exposure signs/symptoms

Section 4. First-aid measures

Eye contact	: Adverse symptoms may include the following: pain or irritation watering redness
Inhalation	: No specific data.
Skin contact	: Adverse symptoms may include the following: irritation redness
Ingestion	: No specific data.
<u>Indication of immediate medical attention and special treatment needed, if necessary</u>	
Notes to physician	: Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
Specific treatments	: No specific treatment.
Protection of first-aiders	: No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Wash contaminated clothing thoroughly with water before removing it, or wear gloves.
See toxicological information (Section 11)	

Section 5. Fire-fighting measures

<u>Extinguishing media</u>	
Suitable extinguishing media	: Use an extinguishing agent suitable for the surrounding fire.
Unsuitable extinguishing media	: None known.
Specific hazards arising from the chemical	: No specific fire or explosion hazard.
Hazardous thermal decomposition products	: Decomposition products may include the following materials: carbon dioxide carbon monoxide sulfur oxides metal oxide/oxides
Special protective actions for fire-fighters	: Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.
Special protective equipment for fire-fighters	: Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

Section 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

For non-emergency personnel	: No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.
For emergency responders	: If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".
Environmental precautions	: Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods and materials for containment and cleaning up

Section 6. Accidental release measures

- Small spill** : Move containers from spill area. Avoid dust generation. Using a vacuum with HEPA filter will reduce dust dispersal. Place spilled material in a designated, labeled waste container. Dispose of via a licensed waste disposal contractor.
- Large spill** : Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Avoid dust generation. Do not dry sweep. Vacuum dust with equipment fitted with a HEPA filter and place in a closed, labeled waste container. Dispose of via a licensed waste disposal contractor. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

Section 7. Handling and storage

Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8). Persons with a history of skin sensitization problems should not be employed in any process in which this product is used. Do not get in eyes or on skin or clothing. Do not ingest. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.

- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

- Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination.

Section 8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

Ingredient name	Exposure limits
Distillates (petroleum), solvent-dewaxed heavy paraffinic	<p>CA Alberta Provincial (Canada, 4/2009). 8 hrs OEL: 5 mg/m³ 8 hours. Form: Mist 15 min OEL: 10 mg/m³ 15 minutes. Form: Mist</p> <p>CA Quebec Provincial (Canada, 1/2014). TWAEV: 5 mg/m³ 8 hours. Form: mist STEV: 10 mg/m³ 15 minutes. Form: mist</p> <p>CA Ontario Provincial (Canada, 7/2015). TWA: 5 mg/m³ 8 hours. Form: mist STEL: 10 mg/m³ 15 minutes. Form: mist</p>
Mineral Oil	<p>CA Alberta Provincial (Canada, 4/2009). 8 hrs OEL: 5 mg/m³ 8 hours. Form: Mist 15 min OEL: 10 mg/m³ 15 minutes. Form: Mist</p> <p>CA Ontario Provincial (Canada, 7/2015). TWA: 5 mg/m³ 8 hours. Form: mist STEL: 10 mg/m³ 15 minutes. Form: mist</p> <p>CA Quebec Provincial (Canada, 1/2014). TWAEV: 5 mg/m³ 8 hours. Form: mist STEV: 10 mg/m³ 15 minutes. Form: mist</p>

Section 8. Exposure controls/personal protection

- Appropriate engineering controls** : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.
- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.
- Individual protection measures**
- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: chemical splash goggles.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated.
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

Section 9. Physical and chemical properties

Appearance

- Physical state** : Solid. [grease]
- Color** : Tan.
- Odor** : Mild. Petroleum oil
- Odor threshold** : Not available.
- pH** : Not applicable.
- Melting point** : Not available.
- Boiling point** : Not available.
- Flash point** : Not available.
- Evaporation rate** : Not available.
- Flammability (solid, gas)** : Flammable in the presence of the following materials or conditions: open flames, sparks and static discharge and heat.
- Lower and upper explosive (flammable) limits** : Not available.
- Vapor pressure** : Not available.

Section 9. Physical and chemical properties

Vapor density	: Not available.
Relative density	: 0.96 g/cm ³
Solubility	: Insoluble in the following materials: cold water.
Partition coefficient: n-octanol/water	: Not available.
Auto-ignition temperature	: Not available.
Decomposition temperature	: Not available.
Viscosity	: Kinematic (40°C (104°F)): >0.21 cm ² /s (>21 cSt)

Section 10. Stability and reactivity

Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
Chemical stability	: The product is stable.
Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
Conditions to avoid	: No specific data.
Incompatible materials	: No specific data.
Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

Section 11. Toxicological information

Information on toxicological effects

Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
Distillates (petroleum), solvent-dewaxed heavy paraffinic	LD50 Dermal	Rabbit	>5000 mg/kg	-
Mineral Oil	LD50 Oral	Rat	>5000 mg/kg	-
	LD50 Dermal	Rabbit	>5000 mg/kg	-
	LD50 Oral	Rat	>5000 mg/kg	-
Benzenesulfonic acid, C10-16-alkyl derivs.	LD50 Dermal	Rabbit	2000 mg/kg	-
	LD50 Oral	Rat	775 mg/kg	-
Sulfonic acids, petroleum, calcium salts	LD50 Dermal	Rabbit	>5 g/kg	-
	LD50 Oral	Rat	>5 g/kg	-
calcium dodecylbenzenesulphonate	LD50 Oral	Rat	1300 mg/kg	-
	LD50 Oral	Rat	1300 mg/kg	-

Conclusion/Summary : No known significant effects or critical hazards.

Irritation/Corrosion

Not available.

Conclusion/Summary

Skin : No known significant effects or critical hazards.

Eyes : Causes eye irritation.

Respiratory : No known significant effects or critical hazards.

Sensitization

Conclusion/Summary

Skin : No known significant effects or critical hazards.

Respiratory : Sensitization not suspected for humans.

Mutagenicity

Section 11. Toxicological information

Conclusion/Summary : There are no data available on the mixture itself. Mutagenicity not suspected for humans.

Carcinogenicity

Conclusion/Summary : There are no data available on the mixture itself. Carcinogenicity not suspected for humans.

Reproductive toxicity

Conclusion/Summary : There are no data available on the mixture itself. Not considered to be dangerous to humans, according to our database.

Teratogenicity

Conclusion/Summary : There are no data available on the mixture itself. Teratogenicity not suspected for humans.

Specific target organ toxicity (single exposure)

Not available.

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Name	Result
Distillates (petroleum), solvent-dewaxed heavy paraffinic Mineral Oil	ASPIRATION HAZARD - Category 1 ASPIRATION HAZARD - Category 1

Information on the likely routes of exposure : Routes of entry anticipated: Oral, Dermal.

Potential acute health effects

Eye contact : Causes serious eye irritation.
Inhalation : No known significant effects or critical hazards.
Skin contact : May cause an allergic skin reaction.
Ingestion : No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

Eye contact : Adverse symptoms may include the following:
 pain or irritation
 watering
 redness
Inhalation : No specific data.
Skin contact : Adverse symptoms may include the following:
 irritation
 redness
Ingestion : No specific data.

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

Potential immediate effects : Not available.

Potential delayed effects : Not available.

Long term exposure

Potential immediate effects : Not available.

Potential delayed effects : Not available.

Potential chronic health effects

Conclusion/Summary : No known significant effects or critical hazards.

General : Once sensitized, a severe allergic reaction may occur when subsequently exposed to very low levels.

Carcinogenicity : No known significant effects or critical hazards.

Section 11. Toxicological information

- Mutagenicity** : No known significant effects or critical hazards.
Teratogenicity : No known significant effects or critical hazards.
Developmental effects : No known significant effects or critical hazards.
Fertility effects : No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

Route	ATE value
Oral	19180.3 mg/kg
Dermal	49497.7 mg/kg

Section 12. Ecological information

Toxicity

Product/ingredient name	Result	Species	Exposure
Benzenesulfonic acid, C10-16-alkyl derivs.	Acute EC50 5.65 mg/l Fresh water	Crustaceans - Ceriodaphnia dubia - Neonate	48 hours

Conclusion/Summary : There are no data available on the mixture itself.

Persistence and degradability

Conclusion/Summary : Not readily biodegradable.

Product/ingredient name	Aquatic half-life	Photolysis	Biodegradability
MILL GREASE NLGI 2	-	-	Not readily

Bioaccumulative potential

Not available.

Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Other adverse effects : No known significant effects or critical hazards.

Section 13. Disposal considerations

Disposal methods : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Section 14. Transport information

Section 14. Transport information

	TDG Classification	DOT Classification	ADR/RID	IMDG	IATA
UN number	Not regulated.	Not regulated.	Not regulated.	Not regulated.	Not regulated.
UN proper shipping name	-	-	-	-	-
Transport hazard class(es)	-	-	-	-	-
Packing group	-	-	-	-	-
Environmental hazards	No.	No.	No.	No.	No.
Additional information	-	-	-	-	-

Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

Transport in bulk according to Annex II of MARPOL and the IBC Code : Not available.

Section 15. Regulatory information

Canadian lists

Canadian NPRI : None of the components are listed.

CEPA Toxic substances : None of the components are listed.

Canada inventory : All components are listed or exempted.

International regulations

Chemical Weapon Convention List Schedules I, II & III Chemicals

Not listed.

Montreal Protocol (Annexes A, B, C, E)

Not listed.

Stockholm Convention on Persistent Organic Pollutants

Not listed.

Rotterdam Convention on Prior Inform Consent (PIC)

Not listed.

UNECE Aarhus Protocol on POPs and Heavy Metals

Not listed.

Inventory list

Australia : All components are listed or exempted.

China : All components are listed or exempted.

Europe : All components are listed or exempted.

Japan : Not determined.

New Zealand : All components are listed or exempted.

Philippines : Not determined.

Section 15. Regulatory information

Republic of Korea	: All components are listed or exempted.
Taiwan	: All components are listed or exempted.
Turkey	: Not determined.
United States	: All components are listed or exempted.

Section 16. Other information

History

Date of issue/Date of revision : 9/21/2016

Date of previous issue : 6/28/2016

Version : 2

Regulatory Department, Chemtool Inc.

Key to abbreviations

: ATE = Acute Toxicity Estimate
 BCF = Bioconcentration Factor
 GHS = Globally Harmonized System of Classification and Labelling of Chemicals
 IATA = International Air Transport Association
 IBC = Intermediate Bulk Container
 IMDG = International Maritime Dangerous Goods
 LogPow = logarithm of the octanol/water partition coefficient
 MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
 UN = United Nations
 HPR = Hazardous Products Regulations

Procedure used to derive the classification

Classification	Justification
EYE IRRITATION - Category 2A	Calculation method
SKIN SENSITIZATION - Category 1	Calculation method

✔ Indicates information that has changed from previously issued version.

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.