



SAFETY DATA SHEET

SYNTHETIC INDUSTRIAL GREASE

SECTION 1: Identification of the substance/mixture and of the company/ undertaking

1.1 Product identifier

Product name : SYNTHETIC INDUSTRIAL GREASE
Product code : GR232.
SDS no. : 1736
Product type : Solid.

1.2 Relevant identified uses of the substance or mixture and uses advised against

Product use: Industrial/ : Industrial applications: Lubricants; grease
Professional use

1.3 Details of the supplier of the safety data sheet

The Timken Corporation
4500 Mt. Pleasant St. NW
North Canton, OH 44720 U.S.A.
234.262.3000

1.4 Emergency telephone number

National advisory body/Poison Centre

Telephone number : INFOTRAC
U.S. and Canada - 800.535.5053
Outside the U.S. and Canada - +1 352.323.3500

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Product definition : Mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Not classified.

Ingredients of unknown toxicity : Percentage of the mixture consisting of ingredient(s) of unknown toxicity: 5%

Ingredients of unknown ecotoxicity : Percentage of the mixture consisting of ingredient(s) of unknown hazards to the aquatic environment: 8%

Classification according to Directive 1999/45/EC [DPD]

The product is not classified as dangerous according to Directive 1999/45/EC and its amendments.

Classification : Not classified.

See Section 16 for the full text of the R phrases or H statements declared above.

See Section 11 for more detailed information on health effects and symptoms.

2.2 Label elements

SECTION 2: Hazards identification

- Signal word** : No signal word.
- Hazard statements** : No known significant effects or critical hazards.
- Prevention** : Not applicable.
- Response** : Not applicable.
- Storage** : Not applicable.
- Disposal** : Not applicable.
- Supplemental label elements** : Contains calcium bis(dinonylnaphthalenesulphonate). May produce an allergic reaction. Safety data sheet available on request.
- Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles** : Not applicable.
- Special packaging requirements**
- Containers to be fitted with child-resistant fastenings** : Not applicable.
- Tactile warning of danger** : Not applicable.

2.3 Other hazards

- Other hazards which do not result in classification** : None known.

SECTION 3: Composition/information on ingredients

Substance/mixture : Mixture

Product/ingredient name	Identifiers	%	Classification		Type
			67/548/EEC	Regulation (EC) No. 1272/2008 [CLP]	
Dec-1-ene, homopolymer, hydrogenated Dec-1-ene, oligomers, hydrogenated	EC: 500-183-1	60-100	Xn; R65	Asp. Tox. 1, H304	[1]
azelaic acid	CAS: 68037-01-4 EC: 204-669-1	1-5	Not classified.	Eye Irrit. 2, H319	[1]
4,4'-methylene bis (dibutyldithiocarbamate)	CAS: 123-99-9 EC: 233-593-1 CAS: 10254-57-6	1-5	R53 See Section 16 for the full text of the R-phrases declared above.	Aquatic Chronic 4, H413 See Section 16 for the full text of the H statements declared above.	[1]

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs or vPvBs or have been assigned a workplace exposure limit and hence require reporting in this section.

Type

- [1] Substance classified with a health or environmental hazard
 [2] Substance with a workplace exposure limit
 [3] Substance meets the criteria for PBT according to Regulation (EC) No. 1907/2006, Annex XIII
 [4] Substance meets the criteria for vPvB according to Regulation (EC) No. 1907/2006, Annex XIII
 [5] Substance of equivalent concern

Occupational exposure limits, if available, are listed in Section 8.

SECTION 4: First aid measures

4.1 Description of first aid measures

- Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.
- Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur. In case of inhalation of decomposition products in a fire, symptoms may be delayed. The exposed person may need to be kept under medical surveillance for 48 hours.
- Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur.
- Ingestion** : Wash out mouth with water. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training.

4.2 Most important symptoms and effects, both acute and delayed

Potential acute health effects

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

Over-exposure signs/symptoms

- Eye contact** : No specific data.
- Inhalation** : No specific data.
- Skin contact** : No specific data.
- Ingestion** : No specific data.

4.3 Indication of any immediate medical attention and special treatment needed

- Notes to physician** : In case of inhalation of decomposition products in a fire, symptoms may be delayed. The exposed person may need to be kept under medical surveillance for 48 hours.
- Specific treatments** : No specific treatment.

SECTION 5: Firefighting measures

5.1 Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

5.2 Special hazards arising from the substance or mixture

- Hazards from the substance or mixture** : No specific fire or explosion hazard.
- Hazardous thermal decomposition products** : Decomposition products may include the following materials:
carbon dioxide
carbon monoxide
nitrogen oxides
sulfur oxides
metal oxide/oxides

5.3 Advice for firefighters

- Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

SECTION 5: Firefighting measures

- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilt material. Put on appropriate personal protective equipment.
- For emergency responders** : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

6.2 Environmental precautions

- : Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

6.3 Methods and material for containment and cleaning up

- Small spill** : Move containers from spill area. Vacuum or sweep up material and place in a designated, labelled waste container. Dispose of via a licensed waste disposal contractor.
- Large spill** : Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Vacuum or sweep up material and place in a designated, labelled waste container. Dispose of via a licensed waste disposal contractor.

6.4 Reference to other sections

- : See Section 1 for emergency contact information.
See Section 8 for information on appropriate personal protective equipment.
See Section 13 for additional waste treatment information.

SECTION 7: Handling and storage

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

7.1 Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8).
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

7.2 Conditions for safe storage, including any incompatibilities

Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination.

7.3 Specific end use(s)

- Recommendations** : Not available.
- Industrial sector specific solutions** : Not available.

SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

8.1 Control parameters

Occupational exposure limits

No exposure limit value known.

Recommended monitoring procedures : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to monitoring standards, such as the following: European Standard EN 689 (Workplace atmospheres - Guidance for the assessment of exposure by inhalation to chemical agents for comparison with limit values and measurement strategy) European Standard EN 14042 (Workplace atmospheres - Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents) European Standard EN 482 (Workplace atmospheres - General requirements for the performance of procedures for the measurement of chemical agents) Reference to national guidance documents for methods for the determination of hazardous substances will also be required.

DNELs/DMELs

No DNELs/DMELs available.

PNECs

No PNECs available

8.2 Exposure controls

Appropriate engineering controls : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

Individual protection measures

Hygiene measures : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

Eye/face protection : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.

Skin protection

Hand protection : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Body protection : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Other skin protection : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Respiratory protection : Use a properly fitted, particulate filter respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

Environmental exposure controls : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance

Physical state	: Solid. [grease]
Colour	: Purple.
Odour	: Characteristic.
pH	: Not applicable.
Melting point/freezing point	: Not available.
Initial boiling point and boiling range	: Not available.
Flash point	: Not available.
Evaporation rate	: Not available.
Flammability (solid, gas)	: Flammable in the presence of the following materials or conditions: open flames, sparks and static discharge and heat.
Upper/lower flammability or explosive limits	: Not available.
Vapour pressure	: Not available.
Vapour density	: Not available.
Density	: 0.87 g/cm ³
Solubility(ies)	: Insoluble in the following materials: cold water.
Partition coefficient: n-octanol/water	: Not available.
Auto-ignition temperature	: Not available.
Decomposition temperature	: Not available.
Viscosity	: Kinematic (40°C (104°F)): >0.21 cm ² /s (>21 cSt)
Explosive properties	: Not available.
Oxidising properties	: Not available.

9.2 Other information

VOC	: 0 g/L
VOC Method	: ASTM E 1868

No additional information.

SECTION 10: Stability and reactivity

10.1 Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
10.2 Chemical stability	: The product is stable.
10.3 Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
10.4 Conditions to avoid	: No specific data.
10.5 Incompatible materials	: No specific data.
10.6 Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
azelaic acid	LD50 Oral	Rat	>5 g/kg	-
4,4'-methylene bis(dibutylthiocarbamate)	LD50 Oral	Rat	16000 mg/kg	-

Conclusion/Summary : No known significant effects or critical hazards.

Acute toxicity estimates

SECTION 11: Toxicological information

Not available.

Irritation/Corrosion

Product/ingredient name	Result	Species	Score	Exposure	Observation
azelaic acid	Eyes - Mild irritant Skin - Mild irritant	Rabbit Rabbit	- -	3 milligrams 24 hours 500 milligrams	- -

Conclusion/Summary

- Skin** : No known significant effects or critical hazards.
- Eyes** : No known significant effects or critical hazards.
- Respiratory** : No known significant effects or critical hazards.

Sensitisation

Conclusion/Summary

- Skin** : May cause an allergic skin reaction.
- Respiratory** : Sensitisation not suspected for humans.

Mutagenicity

Conclusion/Summary

- : There are no data available on the mixture itself. Mutagenicity not suspected for humans.

Carcinogenicity

Conclusion/Summary

- : There are no data available on the mixture itself. Carcinogenicity not suspected for humans.

Reproductive toxicity

Conclusion/Summary

- : There are no data available on the mixture itself. Not considered to be dangerous to humans, according to our database.

Teratogenicity

Conclusion/Summary

- : There are no data available on the mixture itself. Teratogenicity not suspected for humans.

Specific target organ toxicity (single exposure)

Not available.

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Product/ingredient name	Result
Dec-1-ene, homopolymer, hydrogenated Dec-1-ene, oligomers, hydrogenated	ASPIRATION HAZARD - Category 1

Information on the likely routes of exposure

- : Routes of entry anticipated: Oral, Dermal.

Potential acute health effects

- Eye contact** : No known significant effects or critical hazards.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

- Eye contact** : No specific data.
- Inhalation** : No specific data.
- Skin contact** : No specific data.
- Ingestion** : No specific data.

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

SECTION 11: Toxicological information

Potential immediate effects : Not available.

Potential delayed effects : Not available.

Long term exposure

Potential immediate effects : Not available.

Potential delayed effects : Not available.

Potential chronic health effects

Conclusion/Summary : No known significant effects or critical hazards.

General : No known significant effects or critical hazards.

Carcinogenicity : No known significant effects or critical hazards.

Mutagenicity : No known significant effects or critical hazards.

Teratogenicity : No known significant effects or critical hazards.

Developmental effects : No known significant effects or critical hazards.

Fertility effects : No known significant effects or critical hazards.

Other information : Not available.

SECTION 12: Ecological information**12.1 Toxicity**

Conclusion/Summary : There are no data available on the mixture itself.

12.2 Persistence and degradability

Conclusion/Summary : This product has not been tested for biodegradation. Not expected to be rapidly degradable.

Product/ingredient name	Aquatic half-life	Photolysis	Biodegradability
SYNTHETIC INDUSTRIAL GREASE	-	-	Not readily

12.3 Bioaccumulative potential

Product/ingredient name	LogP _{ow}	BCF	Potential
Dec-1-ene, homopolymer, hydrogenated Dec-1-ene, oligomers, hydrogenated azelaic acid	>6.5	-	high
4,4'-methylene bis (dibutyldithiocarbamate)	1.57	238 to 288	low
	-	10.86	low

12.4 Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Mobility : Not available.

12.5 Results of PBT and vPvB assessment

PBT : Not applicable.

vPvB : Not applicable.

12.6 Other adverse effects : No known significant effects or critical hazards.

SECTION 13: Disposal considerations

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

13.1 Waste treatment methods

Product

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.

Hazardous waste : Within the present knowledge of the supplier, this product is not regarded as hazardous waste, as defined by EU Directive 91/689/EEC.

Packaging

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.

Special precautions : This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.

SECTION 14: Transport information

	ADR/RID	ADN	IMDG	IATA
14.1 UN number	Not regulated.	Not regulated.	Not regulated.	Not regulated.
14.2 UN proper shipping name	-	-	-	-
14.3 Transport hazard class(es)	-	-	-	-
14.4 Packing group	-	-	-	-
14.5 Environmental hazards	No.	No.	No.	No.
Additional information	-	-	-	-

14.6 Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code : Not available.

SECTION 15: Regulatory information**15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture****EU Regulation (EC) No. 1907/2006 (REACH)****Annex XIV - List of substances subject to authorisation****Substances of very high concern**

None of the components are listed.

Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles : Not applicable.

Other EU regulations

Europe inventory EINECS/ELINCS : All components are listed or exempted.

Black List Chemicals (76/464/EEC) : Not listed

Priority List Chemicals (793/93/EEC) : Not listed

Integrated pollution prevention and control list (IPPC) - Air : Not listed

Integrated pollution prevention and control list (IPPC) - Water : Not listed

Seveso Directive

This product is not controlled under the Seveso Directive.

International regulations

International lists :

- Europe inventory EINECS/ELINCS**: All components are listed or exempted.
- Australia inventory (AICS)**: Not determined.
- China inventory (IECSC)**: All components are listed or exempted.
- Japan inventory**: Not determined.
- Korea inventory**: Not determined.
- Malaysia Inventory (EHS Register)**: Not determined.
- New Zealand Inventory of Chemicals (NZIoC)**: Not determined.
- Philippines inventory (PICCS)**: Not determined.
- Taiwan inventory (CSNN)**: Not determined.
- United States inventory (TSCA 8b)**: All components are listed or exempted.
- Canada inventory**: All components are listed or exempted.

Chemical Weapons Convention List Schedule I Chemicals : Not listed

Chemical Weapons Convention List Schedule II Chemicals : Not listed

Chemical Weapons Convention List Schedule III Chemicals : Not listed

15.2 Chemical Safety Assessment : This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

✔ Indicates information that has changed from previously issued version.

- Abbreviations and acronyms** : ATE = Acute Toxicity Estimate
 CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
 DMEL = Derived Minimal Effect Level
 DNEL = Derived No Effect Level
 EUH statement = CLP-specific Hazard statement
 PBT = Persistent, Bioaccumulative and Toxic
 PNEC = Predicted No Effect Concentration
 RRN = REACH Registration Number
 vPvB = Very Persistent and Very Bioaccumulative

Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Classification	Justification
Not classified.	

- Full text of abbreviated H statements** : H304 May be fatal if swallowed and enters airways.
 H319 Causes serious eye irritation.
 H413 May cause long lasting harmful effects to aquatic life.
- Full text of classifications [CLP/GHS]** : Aquatic Chronic 4, H413 LONG-TERM AQUATIC HAZARD - Category 4
 Asp. Tox. 1, H304 ASPIRATION HAZARD - Category 1
 Eye Irrit. 2, H319 SERIOUS EYE DAMAGE/ EYE IRRITATION - Category 2
- Full text of abbreviated R phrases** : R65- Harmful: may cause lung damage if swallowed.
 R53- May cause long-term adverse effects in the aquatic environment.
- Full text of classifications [DSD/DPD]** : Xn - Harmful
- Date of issue/ Date of revision** : 10/29/2015
- Date of previous issue** : No previous validation
- Version** : 1

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.