

# SAFETY DATA SHEET

# TACKY MILL GREASE

#### Section 1. Identification **Product identifier** : TACKY MILL GREASE Other means of : Not available. identification **Product type** : Solid. **Product code** : GR183. SDS# : 1747 Relevant identified uses of the substance or mixture and uses advised against **Product use: For** : Industrial applications: Lubricants; grease. professional use only. **Supplier's details** : The Timken Corporation 4500 Mt. Pleasant St. NW North Canton, OH 44720 U.S.A. 234.262.3000 **Emergency telephone** : INFOTRAC number (with hours of U.S. and Canada - 800.535.5053 Outside the U.S. and Canada - +1 352.323.3500 operation)

# Section 2. Hazard identification

Classification of the substance or mixture	:	EYE IRRITATION - Category 2A SKIN SENSITIZATION - Category 1
GHS label elements		
Hazard pictograms	:	
Signal word	:	Warning
Hazard statements	:	Causes serious eye irritation. May cause an allergic skin reaction.
Precautionary statements		
Prevention	:	Wear protective gloves. Wear eye or face protection. Avoid breathing dust. Wash hands thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace.
Response	:	IF ON SKIN: Wash with plenty of soap and water. Take off contaminated clothing and wash it before reuse. If skin irritation or rash occurs: Get medical attention. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention.
Storage	:	Not applicable.
Disposal	:	Dispose of contents and container in accordance with all local, regional, national and international regulations.
Other hazards which do not result in classification	:	None known.

# Section 2. Hazard identification

### Section 3. Composition/information on ingredients

### Substance/mixture

: Mixture

Other means of identification

: Not available.

### **CAS number/other identifiers**

Ingredient name	% (w/w)	CAS number
Mineral Oil	15-40	mixture
Benzenesulfonic acid, C10-16-alkyl derivs.	3-7	68584-22-5
Sulfonic acids, petroleum, calcium salts	3-7	61789-86-4
diboron calcium tetraoxide	1-5	13701-64-9
calcium dodecylbenzenesulphonate	1-5	26264-06-2
N-1-naphthylaniline	0.1-1	90-30-2

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

### Section 4. First-aid measures

#### Description of necessary first aid measures : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower Eye contact eyelids. Check for and remove any contact lenses. Continue to rinse for at least 10 minutes. Get medical attention. Inhalation Remove victim to fresh air and keep at rest in a position comfortable for breathing. ÷. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Get medical attention if adverse health effects persist or are severe. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband. Skin contact : Wash with plenty of soap and water. Remove contaminated clothing and shoes. Wash contaminated clothing thoroughly with water before removing it, or wear gloves. Continue to rinse for at least 10 minutes. Get medical attention. In the event of any complaints or symptoms, avoid further exposure. Wash clothing before reuse. Clean shoes thoroughly before reuse. : Wash out mouth with water. Remove dentures if any. Remove victim to fresh air Ingestion and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Get medical attention if adverse health effects persist or are severe. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband. Most important symptoms/effects, acute and delayed Potential acute health effects Eye contact : Causes serious eye irritation. No known significant effects or critical hazards. Inholotic

Innalation	: No known significant effects or critical hazard
Skin contact	: May cause an allergic skin reaction.

- : May cause an allergic skin reaction. Ingestion
  - : No known significant effects or critical hazards.

**Over-exposure signs/symptoms** 

Validated on 12/20/2016.

# Section 4. First-aid measures

Eye contact	:	Adverse symptoms may include the following: pain or irritation watering redness
Inhalation	1	No specific data.
Skin contact	:	Adverse symptoms may include the following: irritation redness
Ingestion	:	No specific data.
Indication of immediate med	dica	l attention and special treatment needed, if necessary
Notes to physician	:	Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
Specific treatments	:	No specific treatment.
Protection of first-aiders	:	No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Wash contaminated clothing thoroughly with water before removing it, or wear gloves.
<b>O</b> • • • • • • • • • • • • • • • • • • •		

See toxicological information (Section 11)

# Section 5. Fire-fighting measures

Extinguishing media	
Suitable extinguishing media	: Use an extinguishing agent suitable for the surrounding fire.
Unsuitable extinguishing media	: None known.
Specific hazards arising from the chemical	: No specific fire or explosion hazard.
Hazardous thermal decomposition products	: Decomposition products may include the following materials: carbon dioxide carbon monoxide sulfur oxides metal oxide/oxides
Special protective actions for fire-fighters	: Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.
Special protective equipment for fire-fighters	<ul> <li>Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.</li> </ul>

# Section 6. Accidental release measures

Personal precautions, protec	tiv	e equipment and emergency procedures
For non-emergency personnel	:	No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.
For emergency responders	:	If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".
Environmental precautions	:	Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).
Methods and materials for co	ont	ainment and cleaning up

# Section 6. Accidental release measures

Small spill	: Move containers from spill area. Avoid dust generation. Using a vacuum with HEPA filter will reduce dust dispersal. Place spilled material in a designated, labeled waste container. Dispose of via a licensed waste disposal contractor.
Large spill	: Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Avoid dust generation. Do not dry sweep. Vacuum dust with equipment fitted with a HEPA filter and place in a closed, labeled waste container. Dispose of via a licensed waste disposal contractor. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

# Section 7. Handling and storage

Precautions for safe handling	L	
Protective measures	:	Put on appropriate personal protective equipment (see Section 8). Persons with a history of skin sensitization problems should not be employed in any process in which this product is used. Do not get in eyes or on skin or clothing. Do not ingest. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.
Advice on general occupational hygiene	:	Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.
Conditions for safe storage, including any incompatibilities	:	Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination.

# Section 8. Exposure controls/personal protection

### **Control parameters**

**Occupational exposure limits** 

Ingredient name		Exposure limits
Mineral Oil		CA Alberta Provincial (Canada, 4/2009). 8 hrs OEL: 5 mg/m <sup>3</sup> 8 hours. Form: Mist 15 min OEL: 10 mg/m <sup>3</sup> 15 minutes. Form: Mist CA Quebec Provincial (Canada, 1/2014). TWAEV: 5 mg/m <sup>3</sup> 8 hours. Form: mist STEV: 10 mg/m <sup>3</sup> 15 minutes. Form: mist
Appropriate engineering controls	: Good general ventilation should be s contaminants.	ufficient to control worker exposure to airborne
Environmental exposure controls	they comply with the requirements of	rocess equipment should be checked to ensure f environmental protection legislation. In some ineering modifications to the process ce emissions to acceptable levels.
ndividual protection meas	<u>ures</u>	
Hygiene measures	eating, smoking and using the lavato Appropriate techniques should be us Contaminated work clothing should r	roughly after handling chemical products, before bry and at the end of the working period. ted to remove potentially contaminated clothing. not be allowed out of the workplace. Wash g. Ensure that eyewash stations and safety location.
Validated on 12/20/2016.		4/10

# Section 8. Exposure controls/personal protection

•	• •
Eye/face protection	: Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: chemical splash goggles.
Skin protection	
Hand protection	: Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated.
Body protection	<ul> <li>Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.</li> </ul>
Other skin protection	<ul> <li>Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.</li> </ul>
Respiratory protection	: Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

# Section 9. Physical and chemical properties

<u>Appearance</u>		
Physical state	:	Solid. [grease]
Color	:	Black.
Odor	:	Mild. Petroleum oil
Odor threshold	:	Not available.
рН	:	Not applicable.
Melting point	:	Not available.
Boiling point	:	Not available.
Flash point	:	Not available.
Evaporation rate	:	Not available.
Flammability (solid, gas)	1	Flammable in the presence of the following materials or conditions: open flames, sparks and static discharge.
Lower and upper explosive (flammable) limits	:	Not available.
Vapor pressure	:	Not available.
Vapor density	:	Not available.
Relative density	:	0.96 g/cm³
Solubility	:	Insoluble in the following materials: cold water.
Partition coefficient: n- octanol/water	1	Not available.
Auto-ignition temperature	:	Not available.
Decomposition temperature	:	Not available.
Viscosity	:	Not available.

# Section 10. Stability and reactivity

Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
Chemical stability	: The product is stable.
Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
Conditions to avoid	: No specific data.
Incompatible materials	: No specific data.
Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

# Section 11. Toxicological information

### Information on toxicological effects

#### Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
Mineral Oil	LD50 Dermal	Rabbit	>5000 mg/kg	-
	LD50 Oral	Rat	>5000 mg/kg	-
Benzenesulfonic acid, C10-16-alkyl derivs.	LD50 Dermal	Rabbit	2000 mg/kg	-
5	LD50 Oral	Rat	775 mg/kg	-
Sulfonic acids, petroleum, calcium salts	LD50 Dermal	Rabbit	>5 g/kg	-
	LD50 Oral	Rat	>5 g/kg	-
N-1-naphthylaniline	LD50 Dermal	Rabbit	>5000 mg/kg	-
	LD50 Oral	Rat	1625 mg/kg	-

Conclusion/Summary

: No known significant effects or critical hazards.

Irritation/Corrosion

Product/ingredient name	Result	Species	Score	Exposure	Observation
N-1-naphthylaniline	Skin - Mild irritant Skin - Mild irritant Skin - Mild irritant	Rabbit Rabbit Rabbit	-	1008 hours 5 Percent Intermittent 50 Percent 4 hours 5 Percent	-

Conclusion/Summary	
Skin	: No known significant effects or critical hazards.
Eyes	: Causes eye irritation.
Respiratory	: No known significant effects or critical hazards.
<b>Sensitization</b>	
<b>Conclusion/Summary</b>	
Skin	: May cause an allergic skin reaction.
Respiratory	: Sensitization not suspected for humans.
Mutagenicity	
Conclusion/Summary	: There are no data available on the mixture itself. Mutagenicity not suspected for humans.
<b>Carcinogenicity</b>	
Conclusion/Summary	: There are no data available on the mixture itself. Carcinogenicity not suspected for humans.
Reproductive toxicity	
Conclusion/Summary	: There are no data available on the mixture itself. Not considered to be dangerous to humans, according to our database.
<b>Teratogenicity</b>	
Validated on 12/20/2016.	6/10

Conclusion/Summary	<b>Clusion/Summary</b> : There are no data available on the mixture itself. Teratogenicity not suspected for humans.				y not suspected for
Specific target organ toxic	ity (singl	<u>e exposure)</u>			
Not available.					
Specific target organ toxic	itv (repea	ated exposure)			
Name			Category	Route of exposure	Target organs
N-1-naphthylaniline			Category 2	Not determined	Not determined
Aspiration hazard			1		
Name				Result	
Mineral Oil				ASPIRATION HAZARI	D - Category 1
Information on the likely routes of exposure	: Rout	tes of entry anticipate	d: Oral, Dern	hal.	
Potential acute health effect	<u>s</u>				
Eye contact	: Cau	ses serious eye irritat	ion.		
Inhalation	: No k	nown significant effect	cts or critical	hazards.	
Skin contact	: May	cause an allergic skir	n reaction.		
Ingestion	: No k	nown significant effect	cts or critical	hazards.	
Symptoms related to the phy	ysical, cł	nemical and toxicold	ogical charad	<u>cteristics</u>	
Eye contact			nclude the fol	lowing:	
Inhalation	: No s	specific data.			
Skin contact	: Adverse symptoms may include the follo irritation redness			lowing:	
Ingestion : No specific data.					
Delayed and immediate effe	cts and a	also chronic effects	from short a	nd long term exposure	<u>e</u>
Short term exposure					
Potential immediate effects	: Not a	available.			
Potential delayed effects	: Not a	available.			
Long term exposure					
Potential immediate effects	: Not a	available.			
Potential delayed effects	: Not a	available.			
Potential chronic health eff	iects				
Conclusion/Summary	: No k	nown significant effect	cts or critical	hazards.	
General		e sensitized, a severe ery low levels.	e allergic reac	tion may occur when su	bsequently exposed
Carcinogenicity	: No k	nown significant effect	cts or critical	hazards.	
Mutagenicity	: No k	nown significant effect	cts or critical	hazards.	
Teratogenicity	: No k	nown significant effect	cts or critical	hazards.	
<b>Developmental effects</b>	: No k	nown significant effect	cts or critical	hazards.	
Fertility effects	: No k	nown significant effect	cts or critical	hazards.	
Numerical measures of toxic	<u>city</u>				
Acute toxicity estimates					

# Section 11. Toxicological information

Route	ATE value
Oral	16756.8 mg/kg
Dermal	43243.2 mg/kg

# Section 12. Ecological information

Product/ingredient name	Result		Species		Exposure
Benzenesulfonic acid, C10-16-alkyl derivs.	Acute EC50 5.65 mg/l Fresh water		Crustaceans - Ceriodaphni dubia - Neonate		a 48 hours
Conclusion/Summary	: There are no data available on the		mixture itself.		
Persistence and degradabil	<u>ity</u>				
Conclusion/Summary	: This product has no degradable.	t been tested fo	or biodegradation. N	lot expecte	ed to be rapidly
Product/ingredient name	Aquatic half-life		Photolysis Bio		Biodegradability
TACKY MILL GREASE	-		-		Not readily
Bioaccumulative potential					
Product/ingredient name	LogPow	BCF		Potent	ial
N-1-naphthylaniline	4.28 1424			high	
<u>Mobility in soil</u>				1	
Soil/water partition coefficient (Koc)	: Not available.				

# Section 13. Disposal considerations

Other adverse effects

Disposal methods	: The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non- recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.
	matcharana una fana contact with 301, watchway3, arang ana 36wer3,

: No known significant effects or critical hazards.

# Section 14. Transport information

	TDG Classification	DOT Classification	ADR/RID	IMDG	IATA	
UN number	Not regulated.	UN3077	Not regulated.	Not regulated.	Not regulated.	
UN proper shipping name	- ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (calcium dodecylbenzenesulphonate)		-	-	-	
Validated on 12/2	20/2016.				8/	

ransport ir	9	-	1	
	•	-		
				-
		-	-	-
).	No.	No.	No.	No.
	<b>guantity</b> 50000 lbs / 22700 kg The classification of the product is due solely to the presence of one or more US DOT- listed 'Hazardous substances' that are subject to reportable quantity requirements and only applies to shipments of packages greater than, or equal to, the product reportable quantity. Package sizes less than the product reportable quantity are not regulated as hazardous			
uprigl	nt and secure. Ensu	ire that persons		
	<b>Druser : Trans</b> upriging the ev	No.Reportable quantity 50000 lbs / 22700 kg The classification of the product is due solely to the presence of one or more US DOT- listed 'Hazardous substances' that are subject to reportable quantity requirements and only applies to shipments of packages greater than, or equal to, the product reportable quantity. Package sizes less than the product reportable quantity are not regulated as hazardous materials.Dr user:Transport within user's upright and secure. Ensu the event of an accident	No.       No.         Reportable       -         guantity       50000 lbs / 22700 kg         The classification of the product is due solely to the presence of one or more US DOT-listed 'Hazardous substances' that are subject to reportable quantity requirements and only applies to shipments of packages greater than, or equal to, the product reportable quantity. Package sizes less than the product reportable quantity. Package sizes less than the product reportable quantity are not regulated as hazardous materials.         or user :       Transport within user's premises: alw upright and secure. Ensure that persons the event of an accident or spillage.         ording :       Not available.	No.       No.       No.         Reportable quantity 50000 lbs / 22700 kg The classification of the product is due solely to the presence of one or more US DOT- listed 'Hazardous substances' that are subject to reportable quantity requirements and only applies to shipments of packages greater than, or equal to, the product reportable quantity. Package sizes less than the product reportable quantity are not regulated as hazardous materials.       -         or user       : Transport within user's premises: always transport in c upright and secure. Ensure that persons transporting the p the event of an accident or spillage.

# Section 15. Regulatory information

### Canadian lists

 Canadian NPRI
 : None of the components are listed.

 CEPA Toxic substances
 : None of the components are listed.

 Canada inventory
 : All components are listed or exempted.

 International regulations
 Chemical Weapon Convention List Schedules I, II & III Chemicals

 Not listed.
 Not listed.

Validated on 12/20/2016.

### Section 15. Regulatory information

-	Montreal Protocol (Annexes A, B, C, E)							
	Not listed.							
	Stockholm Convention on Persistent Organic Pollutants							
	Not listed.							
	Not listed.							
	Rotterdam Convention on P	rior Inform Consent (PIC)						
	Not listed.							
	UNECE Aarhus Protocol on	POPs and Heavy Metals						
	Not listed.							
	Inventory list							
	Australia	: All components are listed or exempted.						
	China	: All components are listed or exempted.						
	Europe	: All components are listed or exempted.						
	Japan	: All components are listed or exempted.						
	New Zealand	: All components are listed or exempted.						
	Philippines	: Not determined.						
	Popublic of Koroa	· All components are listed or exempted						

Republic of Korea	4	All components are listed or exempted.
Taiwan	1	All components are listed or exempted.

	· · ··································
United States	: All components are listed or exempted.

### Section 16. Other information

H	is	to	ry

: 12/20/2016

Date of issue/Date of revision	: 12/20/2016	
Date of previous issue	: 9/21/2016	
Version	: 1.01	
	Regulatory Department, Chemtool Inc.	
Key to abbreviations	<ul> <li>ATE = Acute Toxicity Estimate BCF = Bioconcentration Factor GHS = Globally Harmonized System of Classification and Labelling of Chemicals IATA = International Air Transport Association IBC = Internediate Bulk Container IMDG = International Maritime Dangerous Goods LogPow = logarithm of the octanol/water partition coefficient MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution) UN = United Nations HPR = Hazardous Products Regulations</li> </ul>	

#### Procedure used to derive the classification

Classification	Justification
	Calculation method Calculation method

#### ✓ Indicates information that has changed from previously issued version.

### Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the abovenamed supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.