

Industry-Accepted Maintenance Practices

To increase application performance and help ensure safety, refer to these “Technology & Maintenance Council (TMC) Recommended Maintenance Practices (RPs)” when handling wheel or drivetrain bearings.

Recommended Practices for Wheel Bearings

RP 618 – Wheel End Adjustment Procedures: Outlines a nine-step procedure to achieve a verifiable wheel bearing end play of 0.001 in. to 0.005 in.

RP 622 – Wheel Seal and Bearing Removal, Installation and Maintenance: Guidelines for acceptable storage, handling and installation of wheel bearings and seals.

RP 631A – Recommendations for Wheel End Lubrication: Operational considerations for inspecting and servicing oil, grease and semi-fluid wheel ends.

RP 640 – Alternate Wheel Bearing Adjustment Systems: Identifies and briefly explains conventional adjustable, pre-adjusted and unitized wheel ends.

RP 644 – Wheel End Conditions Analysis Guide: Guidelines for detecting and evaluating damage to wheel end components (hubcaps, axle spindle nuts, wheel hubs, seals, bearings, lubricant and spindles).

Recommended Practices for Drivetrain Bearings

RP 610A – Driveline Design Criteria and Maintenance Guidelines: Guidelines for the evaluation of drivetrain designs and installation. Following this RP will help optimize bearing performance and minimize NVH (Noise, Vibration, Harshness) of the entire drivetrain.



Visit timken.com/techseries
to enroll in free technical training.

Get more TechTips online at
www.timken.com/techtips

TIMKEN

The Timken team applies their know-how to improve the reliability and performance of machinery in diverse markets worldwide. The company designs, makes and markets high-performance mechanical components, including bearings, gears, belts, chain and related mechanical power transmission products and services.

www.timken.com/aftermarket

Stronger. **Commitment.** Stronger. **Value.** Stronger. **Worldwide.** Stronger. **Together.** | Stronger. **By Design.**